

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

TAMPER-PROOF LABELS OVERVIEW


SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
MV	A77028-000	MV-165051-25-8A	SV7000, Polyester silver (0,077 mm), Acrylic adhesive with „VOID“ Pattern	TTDS-084
TN	F58436-000	TN-165051-25-8A	PE7021, Polyethylene destructive white matt (0,07 mm), Acrylic adhesive	TTDS-091

Quantity per roll: 25.000 PCs

Labels across: 4

Winding: outside

length of roll: 52,1 m






approx. Ø
129-143
[5.079-5.630]

Ø
76,2
[3,00]

Color-appearance
on roll



LABEL BUILD DETAILS	
	SUBSTRATE
	ADHESIVE
	LINER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0,3 [0,012]
LABEL WIDTH:	±0,3 [0,012]
WEB WIDTH:	±0,8 [0,031]
VERTICAL REPEAT:	±0,8 [0,031]*
HORIZONTAL REPEAT:	±0,8 [0,031]*
PRINT POSITIONING:	±0,8 [0,031]*
LEFT MARGIN:	±0,4 [0,016]
QUANTITY:	-0% +2%
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT

DIMENSIONS mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±

MATERIAL: SEE TABLE

FINISH:

DWN	S. Iser / 01.04.2020	DATE	TE Connectivity	
CHK	S. Iser / 01.04.2020	DATE	Name	
APVD	S. Iser / 01.04.2020	DATE	Tamper-proof Label Size „16501“	
PRODUCT SPEC		DATE	SIZE	CAGE CODE
APPLICATION SPEC		DATE	A3	C2290
WEIGHT	MV: 0,008 g TN: 0,006 g	DRAWING NO	C-TAMPER-PROOF	
CUSTOMER DRAWING			SHEET	1 of 1
			REV	A1

All dimensions in mm [inch]
labels are centered on the liner
as long as not declared separately

TAMPER-PROOF SERIES

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[F58436-000](#)