

NUMBER  
C-176766





METRIC

PROJ NO. 592-366  
PROJ NO. 399-355

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST

AMP-1  
REV. 10/78



4  
3  
2  
1

注記;

- 1 適用規格 : 108-5315
- 製品規格 : 114-5147
- 取付適用規格 : 15-507J
- 2 取扱い説明書 : 66ダイヤロン 94V-0
- △材料及び色

NOTES;

- 1 APPLICABLE SPECIFICATIONS
- PRODUCT SPEC. : 108-5315
- APPLICATION SPEC. : 114-5147
- 2 INSTRUCTION SHEET: 15-507J
- △ MATERIAL&COLOR : 66NYLON 94V-0

黒色	BLACK	176766-2
アートグレー	ART GRAY	176766-1
色	COLOR	P/N

1									
B	REVISED	ECH-ND FABR-107-88	I.E	Y	7-DEC -80				
A	ADDED P/N	J-1894	I.K	Y.Y	30-OCT -80				
0	REVISED	J-12829	I.E	S.M	20-NOV -80				
0	RELEASED	J-12829	T.F	S.M	8-MAY -80				
LTR	REVISION RECORD		DR	CHK	DATE				

Copyright © 1990  
AMP (Japan) LTD.  
ALL RIGHTS RESERVED.

**AMP**

AMP (JAPAN), LTD.  
Tokyo, Japan

WIRE RANGE	mm <sup>2</sup> (AWG)	INSULATION DIA	mmφ
SEE TABLE 参考照			
DR.	I. FUJITSUGI	DE.	I. ENOMOTO
CHK.	S. MANABE	APP.	S. MANABE
NAME: アンペア ライオン コネクター			
AMP LATTICE CONN. DUST COVER 12POS			
GENERAL TOLERANCE	SIZE	LOC	NUMBER
0<math>C</math>K 10 : ±0.2	B	J	C-176766
10<math>C</math>K 30 : ±0.35	SCALE 2-1		
30<math>C</math>K 100 : ±0.5	REV. B		
ANGLES : ±3'	SHEET 1 OF 1		

CUSTOMER DRAWING

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[176766-1](#)