



REVISIONS					
P	LTR	DESCRIPTION	DATE	DMN	APVD
E	REVISED PER	ECO-15-015186	28/MAR/16	PY	YM




1. CHARACTERISTIC IMPEDANCE: 100±10 OHMS (MEASURED DIFFERENTIALLY)

2 LABEL INFORMATION:



3 LABEL INFORMATION:



4. SEE SHEET 2 FOR WIRING SCHEMATIC.


5. ROHS COMPLIANCE: PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE CONNECTIVITY SPECIFICATION TEC-138-702.

24 AWG	15	+0.12 -0	METERS	1-2032757-6
24 AWG	14	+0.12 -0	METERS	1-2032757-5
24 AWG	13	+0.12 -0	METERS	1-2032757-4
24 AWG	12	+0.12 -0	METERS	1-2032757-3
24 AWG	11	+0.12 -0	METERS	1-2032757-2
28 AWG	10	+0.12 -0	METERS	1-2032757-1
28 AWG	9	+0.1 -0	METERS	1-2032757-0
30 AWG	8	+0.1 -0	METERS	2032757-9
30 AWG	7	+0.1 -0	METERS	2032757-8
30 AWG	6	+0.1 -0	METERS	2032757-7
30 AWG	5	+0.1 -0	METERS	2032757-6
30 AWG	4	+0.08 -0	METERS	2032757-5
30 AWG	3	+0.08 -0	METERS	2032757-4
30 AWG	2	+0.08 -0	METERS	2032757-3
30 AWG	1	+0.05 -0	METERS	2032757-2
30 AWG	0.5	+0.05 -0	METERS	2032757-1
CABLE GAUGE	L			PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN	20APR2009	TE Connectivity	
mm	0 PLC ± -	DRW	T. SMITH	CABLE ASSY.SFP+ TO SFP+ NI_PLATED	
	1 PLC ± -	CHK	D. LAWRENCE	APPLICATION SPEC	
	2 PLC ± -	APPD	D. LAWRENCE	SIZE	CAGE CODE
	3 PLC ± -	NAME		A1	00779
	4 PLC ± -	PRODUCT SPEC		DRAWING NO	2032757
	ANGLES ± -	RESTRICTED TO		SCALE	1:1
MATERIAL	FINISH	WEIGHT	0	SHEET	1 OF 2
		CUSTOMER DRAWING		REV	E

REVISIONS				
REV	DATE	DESCRIPTION	BY	APP'D
-	-	SEE SHEET 1	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SMITH 20APR2009	TE Connectivity
DIMENSIONS: mm		CHK D.LAWRENCE 20APR2009	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± - 1. PLC ± - 2. PLC ± - 3. PLC ± - 4. PLC ± - ANGLES ± - FINISH -		APP'D D.LAWRENCE 20APR2009	NAME CABLE ASSY,SFP+ TO SFP+ NI_PLATED
		PRODUCT SPEC -	RESTRICTED TO -
MATERIAL -		APPLICATION SPEC -	SIZE A1
CUSTOMER DRAWING		WEIGHT -	CAGE CODE 00779
		DRAWING NO. 2032757	SCALE 1:1
		SHEET 2 OF 2	REV E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2032757-2](#)