



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	ECR-14-015049		13OCT2014	GSK	BvH
A2	ECR-16-003945		16MAR2016	GSK	BvH

NOTES:
 Tolerances cable lengths:
 0m to 0.5m +30mm
 0.5m to 1.0m +50mm
 1.0m to 3.0m +100mm
 < 3.0m +1.5%



TECHNICAL DATA	
Operating voltage	max. 250 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)



PUR CABLE	
No./diameter of wires	3 x 0.34 mm ²
Wire isolation	PP (br, bl, bk)
C-track properties	5 million
Jacket	PUR (UL/CSA)
Outer diameter	approx. 4.3 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-25...+80 °C

LENGTH "L"	MATERIAL	JACKET COLOR	TE PN	DESCRIPTION	ITEM
3 pos	PVC	Black	1-2273120-5	3x22AWG PVC 2.0m	10
			1-2273120-4	3x22AWG PVC 1.5m	9
			1-2273120-3	3x22AWG PVC 1.0m	8
			1-2273120-2	3x22AWG PVC 0.6m	7
			1-2273120-1	3x22AWG PVC 0.3m	6
3 pos	PUR	Black	2273120-5	3x22AWG PUR 2.0m	5
			2273120-4	3x22AWG PUR 1.5m	4
			2273120-3	3x22AWG PUR 1.0m	3
			2273120-2	3x22AWG PUR 0.6m	2
			2273120-1	3x22AWG PUR 0.3m	1

PVC CABLE	
No./diameter of wires	3 x 0.34 mm ²
Wire isolation	PVC (br, bl, bk)
C-track properties	
Jacket	PVC (UL/CSA)
Outer diameter	approx. 4.6 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	-30...+80 °C
Temperature range (mobile)	-5...+80 °C

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN YATHISH.C 29NOV2013	STE TE Connectivity
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	CHK B.VELDHOVEN 29NOV2013	
MATERIAL -	FINISH -	APVD A.VAN ZANDVOORT 29NOV2013	NAME M12 ANGLED PLUG TO M12 STRGT SOCKET AA
		PRODUCT SPEC 108-19483	SIZE A3 CAGE CODE 00779 DRAWING NO C-2273120 RESTRICTED TO -
		APPLICATION SPEC 114-32127	SCALE NTS SHEET 1 OF 1 REV A2
		WEIGHT	CUSTOMER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2273120-1](#)