

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
| | - | SEE SHEET 1 | - | - | - |

| | | | | | | | | | | | |
|------|------------------------------|---------------------------------|----------------------|-------------------|--------------------------------------|---|------------------------|---------|---------|---------|--------------|
| 7 | 2-2308272-4 | CABLE CLAMP7 | CABLE CLAMP BOTTOM | CABLE CLAMP UPPER | 5 | 125 | 14-16 | 9-10 | 7.5-8.5 | 6.5-8 | 20 |
| 6 | 2-2308272-3 | CABLE CLAMP6 | CABLE CLAMP BOTTOM | CABLE CLAMP UPPER | 5 | 100 | 11-14 | 7-8 | 6-7 | 5-6.5 | 16 |
| 5 | 2-2308272-2 | CABLE CLAMP5 | CABLE CLAMP BOTTOM | CABLE CLAMP UPPER | 5 | 100 | 8-10 | 5-7 | 4-5 | - | 21 |
| 4 | 2-2308272-1 | CABLE CLAMP4 | CABLE CLAMP BOTTOM | CABLE CLAMP UPPER | 1-4 | 85 | 11-14 | 7-8 | 6-7 | 5-6 | 16 |
| 3 | 2-2308272-0 | CABLE CLAMP3 | CABLE CLAMP BOTTOM | CABLE CLAMP UPPER | 1-4 | 75 | 9-12 | 6-7 | 5-6 | 4-5 | 12 |
| 2 | 1-2308272-9 | CABLE CLAMP2 | CABLE CLAMP BOTTOM | CABLE CLAMP UPPER | 1-4 | 65 | 7-10 | 5-6 | 4-4.5 | - | 12 |
| 1 | 1-2308272-8 | CABLE CLAMP1 | CABLE CLAMP BOTTOM | CABLE CLAMP UPPER | 1-4 | 65 | 4-7 | 4-5 | 3.5-4 | - | 14 |
| SIZE | PART NO: (CASE Ni-PLATED) | DESCRIPTION (CASE Ni-PLATED) | POS. 1 | POS. 2 | AVAILABLE IN THE HOODS SIZE | WINDOWS FOR LACES, mm ² | 1 CABLE | 2 CABLE | 3 CABLE | 4 CABLE | WEIGHT, g |
| | | | SUB-PART DESCRIPTION | | | | FOR CABLE DIAMETER, mm | | | | |

| | | | | | | | | | | | |
|------|------------------------|---------------------------|----------------------|-------------------|--------------------------------------|---|------------------------|---------|---------|---------|--------------|
| 7 | 1-2308272-7 | CABLE CLAMP7 | CABLE CLAMP BOTTOM | CABLE CLAMP UPPER | 5 | 125 | 14-16 | 9-10 | 7.5-8.5 | 6.5-8 | 20 |
| 6 | 1-2308272-6 | CABLE CLAMP6 | CABLE CLAMP BOTTOM | CABLE CLAMP UPPER | 5 | 100 | 11-14 | 7-8 | 6-7 | 5-6.5 | 16 |
| 5 | 1-2308272-5 | CABLE CLAMP5 | CABLE CLAMP BOTTOM | CABLE CLAMP UPPER | 5 | 100 | 8-10 | 5-7 | 4-5 | - | 21 |
| 4 | 1-2308272-4 | CABLE CLAMP4 | CABLE CLAMP BOTTOM | CABLE CLAMP UPPER | 1-4 | 85 | 11-14 | 7-8 | 6-7 | 5-6 | 16 |
| 3 | 1-2308272-3 | CABLE CLAMP3 | CABLE CLAMP BOTTOM | CABLE CLAMP UPPER | 1-4 | 75 | 9-12 | 6-7 | 5-6 | 4-5 | 12 |
| 2 | 1-2308272-2 | CABLE CLAMP2 | CABLE CLAMP BOTTOM | CABLE CLAMP UPPER | 1-4 | 65 | 7-10 | 5-6 | 4-4.5 | - | 12 |
| 1 | 1-2308272-1 | CABLE CLAMP1 | CABLE CLAMP BOTTOM | CABLE CLAMP UPPER | 1-4 | 65 | 4-7 | 4-5 | 3.5-4 | - | 14 |
| SIZE | PART NO: (CASE RAW) | DESCRIPTION (CASE RAW) | POS. 1 | POS. 2 | AVAILABLE IN THE HOODS SIZE | WINDOWS FOR LACES, mm ² | 1 CABLE | 2 CABLE | 3 CABLE | 4 CABLE | WEIGHT, g |
| | | | SUB-PART DESCRIPTION | | | | FOR CABLE DIAMETER, mm | | | | |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
DIN ISO 2768 m

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

FINISH
-

DWN
KIRAN K
26JUL2016

CHK
GUNASEKHAR G
26JUL2016

APVD
GUNASEKHAR G
26JUL2016

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME
CABLE CLAMPS

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=2308272

RESTRICTED TO
-

SCALE
NTS

SHEET
2 of 2

REV
A1

1471-9 (1/15)

2308272

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2308272-7](#)