




REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD
A		PER ECO-18-020143	31DEC2018	MY FG
B		REV PER ECO-19-013192	27AUG2019	TS GF
C		REV PER ECO-20-006125	30APR2020	AK GF
-	-	-	-	-



1 LABEL INFORMATION FOR 25 GIG PNS (-1 THRU -10): -1 SHOWN.




- 2. SEE SHEET 2 FOR WIRING SCHEMATIC.
- 3. PRODUCT AND PROCESSING MUST MEET THE REQUIREMENTS OF TE SPECIFICATION TEC-138-702.
- 4. CABLE ASSEMBLY TO BE TESTED FOR OPENS, SHORTS AND PROPER EEPROM PROGRAM.
- 5. EEPROM DOES NOT INCLUDE PAGE SWAPPING.
- 6 TEST IN ACCORDANCE WITH IEEE802.3bj.
- 7 DASH NUMBER 41 THRU 46 CONFORM TO 56G, PAM-4 IEEE802.3CD PERFORMANCE REQUIREMENTS.
- 8 LABEL INFORMATION FOR 56 GIG PNS (-41 THRU -46): -41 SHOWN.



STANDARD	GAGE	"L" mm	PART NO	
7	26	3000 +80/-0	4-2333842-6	
	26	2500 +80/-0	4-2333842-5	
	26	2000 +80/-0	4-2333842-4	
	26	1500 +80/-0	4-2333842-3	
	26	1000 +50/-0	4-2333842-2	
	26	500 +50/-0	4-2333842-1	
	6	26	5000 +80/-0	1-2333842-0
		26	4500 +80/-0	2333842-9
		26	4000 +80/-0	2333842-8
		26	3500 +80/-0	2333842-7
26		3000 +80/-0	2333842-6	
26		2500 +80/-0	2333842-5	
26		2000 +80/-0	2333842-4	
26		1500 +80/-0	2333842-3	
26	1000 +50/-0	2333842-2		
26	500 +50/-0	2333842-1		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: M. YI 17APR2018	TE Connectivity
DIMENSIONS: min		CHK: G. FRANKLIN 17APR2018	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: G. FRANKLIN 17APR2018	NAME: CABLE ASSEMBLY, DIRECT ATTACH QSFP 26AWG, 25GIG
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH ±		PRODUCT SPEC: -	RESTRICTED TO: -
MATERIAL: -		APPLICATION SPEC: -	SIZE: A1
FINISH: -		WEIGHT: -	CAGE CODE: 00779
RESTRICTED CUSTOMER		DRAWING NO: 2333842	SCALE: 5:1
		SHEET: 1 OF 2	REV: C

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-



WIRING PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: M. YI 17APR2018	 TE Connectivity										
DIMENSIONS: min		CHK: G. FRANKLIN 17APR2018											
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: G. FRANKLIN 17APR2018	NAME: CABLE ASSEMBLY, DIRECT ATTACH QSFP										
<table border="1"> <tr><td>0 PLC</td><td>±</td></tr> <tr><td>1 PLC</td><td>±</td></tr> <tr><td>2 PLC</td><td>±</td></tr> <tr><td>3 PLC</td><td>±</td></tr> <tr><td>4 PLC</td><td>±</td></tr> </table>		0 PLC	±	1 PLC	±	2 PLC	±	3 PLC	±	4 PLC	±	PRODUCT SPEC: -	SIZE: A1
0 PLC	±												
1 PLC	±												
2 PLC	±												
3 PLC	±												
4 PLC	±												
MATERIAL: -		APPLICATION SPEC: -	CAGE CODE: 00779										
FINISH: -		WEIGHT: -	DRAWING NO: 2333842										
RESTRICTED CUSTOMER		RESTRICTED TO:	SCALE: 5:1										
			SHEET 2 OF 2										
			REV C										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2333842-4](#)