



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	REVISED PER ECO-20-008150	15JUN2020	MY	DZ



- ASSEMBLY TO BE 100% TESTED FOR CONTINUITY, SHORTS, AND OPENS, CABLES ASSEMBLYS ARE ALSO TO BE 100% TESTED FOR SIGNAL INTEGRITY, TO SAS 3.0 REQUIREMENTS.
- ROHS AND REACH COMPLIANCE: PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE SPECIFICATION TEC-138-702.

3 LABEL CENTERED AND LABEL INFORMATION AS BELOW:




4. SEE SHEET #2 FOR WIRING SCHEMATIC.

200	+25 -0	2820332-5
1000	+25 -0	2820332-4
700	+25 -0	2820332-3
500	+25 -0	2820332-2
300	+25 -0	2820332-1
"L"	[MM]	TE P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.YI 16/JUN/2014	TE Connectivity Ltd.	
DIMENSIONS: mm		CHK G.GUTGOLD 16/JUN/2014	C/A, INTERNAL HD MINI SAS, STR TO R/A 100 OHMS, 4X 30 AWG	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD G.GUTGOLD 16/JUN/2014	RESTRICTED TO	
MATERIAL	FINISH	WEIGHT 0	SIZE A2	CAGE CODE 00779
CUSTOMER DRAWING		DRAWING NO C-2820332	SCALE N.T.S.	
		SHEET 1 of 2		REV C2

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-



WIRING PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.YI 16/JUN/2014	TE Connectivity Ltd.			
DIMENSIONS: mm		CHK G.GUTGOLD 16/JUN/2014				
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD G.GUTGOLD 16/JUN/2014 PRODUCT SPEC APPLICATION SPEC	NAME C/A, INTERNAL HD MINI SAS, STR TO R/A 100 OHMS, 4X 30 AWG	
MATERIAL		WEIGHT 0	SIZE A2	CAGE CODE 00779	DRAWING NO C-2820332	RESTRICTED TO
CUSTOMER DRAWING			SCALE N.T.S.	SHEET 2 of 2	REV C2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2820332-4](#)