



PCB Layout

REVISIONS			
REV	DESCRIPTION	DATE	BY
1	INITIAL RELEASE	2002/09/25	GF
2	UPDATE DESCRIPTION	2002/09/25	GF
3	UPDATE DESCRIPTION	2002/09/25	GF

REV	DESCRIPTION	DATE	BY
1	INITIAL RELEASE	2002/09/25	GF
2	UPDATE DESCRIPTION	2002/09/25	GF
3	UPDATE DESCRIPTION	2002/09/25	GF
4	UPDATE DESCRIPTION	2002/09/25	GF
5	UPDATE DESCRIPTION	2002/09/25	GF
6	UPDATE DESCRIPTION	2002/09/25	GF
7	UPDATE DESCRIPTION	2002/09/25	GF
8	UPDATE DESCRIPTION	2002/09/25	GF

- NOTES :
- △ MATERIALS AND FINISH:
 - HOUSING: PA66
 - CONTACTS: BRASS, FINISH: TIN OVER NICKEL UNDERPLATE
 - 2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (RoHS)
 - 3. WIRE TYPES AND SIZES ACCEPTED
 - WIRE RANGE: 12AWG~28AWG.
 - STRIP LENGTH: 5~6mm
 - 4. PACKAGED IN TRAY.
 - 5. CURRENT RATING: 20Amp AC300V.
 - 6. OPERATION TEMPERATURE: -40°C TO +105°C
 - 7. THIS PART NO. IS THE SAME STRUCTURE AS THE SERIES: 2834080
 - THE DATASHEET AND MORE DETAILS PLEASE FOLLOW THE SERIES: 2834080

THIS DRAWING IS A CONTROLLED DOCUMENT.

IMPERIAL FU 200202015
 SHI LANG 200202015

DATE: 2002/09/25

PRODUCT CODE: 109-137148

APPROVAL SIGNATURE: [Signature]

VERSION: 114-137148

CUSTOMER DRAWING: [Signature]

5.00mm Horizontal Entry Screwless Connector

SCALE: 1:1

REV: 8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2834080-4](#)