



POSITION	DESCRIPTION	DATE	BY	APP'D
⑤	SPRING			
④	COVER			
③	LEVER			
②	CONTACT			
①	HOUSING			

  

POSITION	DESCRIPTION	DATE	BY	APP'D
8 POSN				
7 POSN				
6 POSN				
5 POSN				
4 POSN				
3 POSN				
2 POSN				

  

NO. OF POSITIONS	PART NO
8 POSN	2834080-7
7 POSN	2834080-6
6 POSN	2834080-5
5 POSN	2834080-4
4 POSN	2834080-3
3 POSN	2834080-2
2 POSN	2834080-1

- NOTES :
- △ MATERIALS AND FINISH:
    - HOUSING: PA66
    - CONTACTS: BRASS, FINISH: TIN OVER NICKEL UNDERPLATE
  - 2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (RoHS)
  - 3. WIRE TYPES AND SIZES ACCEPTED
  - WIRE RANGE: 12AWG~28AWG.
  - STRIP LENGTH: 5~6mm
  - 4. PACKAGED IN TRAY.
  - 5. CURRENT RATING: 20Amp AC300V.
  - 6. OPERATION TEMPERATURE: -40°C TO +105°C
  - 7. THIS PART NO. IS THE SAME STRUCTURE AS THE SERIES: 2834080
  - THE DATASHEET AND MORE DETAILS PLEASE FOLLOW THE SERIES: 2834080

THIS DRAWING IS A CONTROLLED DOCUMENT.

IMPROVE FU 20DEC2015  
 SHI LANG 20DEC2015

108-137148  
 114-137148

5.00mm Horizontal Entry Screwless Connector

STTE TE Connectivity

SIZE 1 CODE CODE DRAWING NO C-2834080

A200779

SCALE 1:1

SHEET 1 OF 1

REV 3

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2834080-5](#)