



- NOTES :
- ▲ MATERIALS AND FINISH:
 - HOUSING: PA66
 - CONTACTS: BRASS, FINISH: TIN OVER NICKEL UNDERPLATE
 - 2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
 - 3. WIRE TYPES AND SIZES ACCEPTED
 - WIRE RANGE: 20AWG~28AWG.
 - STRIP LENGTH: 5.5mm~6.5mm
 - 4. PACKAGED IN TRAY.
 - 5. CURRENT RATING: 4Amp AC150V.
 - 6. OPERATION TEMPERATURE: -40°C TO +105°C
 - 7. THIS PART NO. IS THE SAME STRUCTURE AS THE SERIES: 2834084
 - THE DATASHEET AND MORE DETAILS PLEASE FOLLOW THE SERIES: 2834084

REV	DATE	BY	APP'D
1	08DEC2015	CF	SM

NO. OF POSN	PART NO	NO. OF POSN	PART NO
21.50	2834084-7	8 POSN	2834084-7
19.00	2834084-6	7 POSN	2834084-6
16.50	2834084-5	6 POSN	2834084-5
14.00	2834084-4	5 POSN	2834084-4
11.50	2834084-3	4 POSN	2834084-3
9.00	2834084-2	3 POSN	2834084-2
6.50	2834084-1	2 POSN	2834084-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

STI TE Connectivity

2.5 45Entry Screwless Connector

DATE: 08DEC2015

REV: 1

SCALE: 1:1

SHEET: 1 OF 1

REV: A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2834084-5](#)