


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - TE Connectivity Ltd. ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
E2		UPDATED WIRE SIZE TO 0.3-1.00mm <sup>2</sup>	17APR18	-	NG
E3		REVISED PER ECO-19-016648	21NOV2019	RS	DR



- MATERIAL:  
 BODY: SEE TABLE  
 SLEEVE: COPPER PER ASTM B152  
 INSULATION: POLYAMIDE 6/6 (NYLON) PER ASTM D4066  
  
 MATERIAL:  
 CUERPO: VER TABLA  
 MANGA: COBRE POR ASTM B152  
 AISLAMIENTO: POLIAMIDA 6/6 (NYLON) POR ASTM D4066
- FINISH:  
 BODY: TIN PLATE 0.002 [.000079]  
 MIN EXT THICK PER ASTM B545  
 SLEEVE: NONE  
 INSULATION, COLOR: RED
- TERMINAR:  
 CUERPO: HOJA DE HOJALATA 0.002 [.000079]  
 ESPESOR MÍNIMO EXT. POR ASTM B545  
 MANGA: NINGUNA  
 COLOR DE, AISLAMIENTO: ROJO
- WIRE RANGE: 0.500 [.019]-1.000 [.039]mm<sup>2</sup> [22-18 AWG]  
 GAMA DE ALAMBRE: 0.500 [.019] -1.000 [.039] mm<sup>2</sup> [22-18 AWG]

LOOSE PIECE PIEZA SUELTA	100	PHOS BRONZE PER ASTM B103 LATON ESTANADO POR ASTM B103	735279
PACKAGE TYPE TIPO DE PAQUETE	QTY CANTIDAD	BODY MATL. CUERPO MATL.	PART NUMBER NÚMERO DE PIEZA

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAVI S 15NOV2019	<b>STE</b> TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK DANIEL ROHDE 15NOV2019		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DANIEL ROHDE 15NOV2019	NAME	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.500 [.019] 4 PLC ± - ANGLES ± -		PRODUCT SPEC	FULLY INSULATED FASTON RCPT 6.35 MM (RED) RECEPTÁCULO FASTON 6.35 MM AISLADO (ROJO)	
MATERIAL SEE TABLE VER TABLA		APPLICATION SPEC	SIZE A3	CAGE CODE 00779
FINISH △		WEIGHT -	DRAWING NO G-735279	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1
			REV E3	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[735279](#)