





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	18JAN2016	N.P	X.X
	A1	PER ECR-16-010253	21JUL2016	N.P	X.X



7. 产品必须符合ROHS与REACH.

WIRES: 0.25mm ² (24AWG)	STANDARD: -001: 0.5m -002: 1.0m -003: 1.5m -004: 3.0m -005: 5.0m -006: 7.0m -007: 10.0m CUSTOMIZATION: -***0: **.0m -***1: **.5m	FIXED: -40°C~80°C FLXIBLE: -25°C~80°C	GRAY	PUR (UL)	RPC-M8-MS-4CON-PUR-***5	4	T4051120004-00X
					RPC-M8-MS-3CON-PUR-***5	3	T4051120003-00X
		FIXED: -10°C~80°C FLXIBLE: -5°C~80°C	BLACK	PVC (UL)	RPC-M8-MS-4CON-PVC-***5	4	T4051110004-00X
					RPC-M8-MS-3CON-PVC-***5	3	T4051110003-00X
CABLE CHARACTERISTIC	LENGTH "L"	CABLE TEMP. RANGE	JACKET COLOR	JACKET MATERIAL	TYPE	POS.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Nick Pan 02DEC2015		 TE Connectivity					
		CHK Kobby Zhao 02DEC2015							
		APVD Xiang Xu 02DEC2015							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.35 3 PLC ±0.25 4 PLC ± ANGLES ±		NAME M8 CABLE STRAIGHT SINGLE ENDED MALE SIDE, UNSHIELDED					
				PRODUCT SPEC 108-106140					
MATERIAL TBD		FINISH -		APPLICATION SPEC -		SIZE A2		CAGE CODE -	
				WEIGHT -		DRAWING NO C-T40511X000X00X		RESTRICTED TO -	
CUSTOMER DRAWING						SCALE 1:1		SHEET 1 OF 1	
						REV A1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4051120004-006](#)