


ITEM	DESCRIPTION	MATERIAL	OTHERS
1	MALE CONTACT	COPPER ALLOY	FLASH GOLD
2	MALE HOUSING	NYLON	BLACK
3	MALE NUT	COPPER ALLOY	NICKEL PLATED
4	OVER-MOLDING	POLYURETHANE	BLUE
5	CABLE	-	-
6	LABEL	-	-
7	FEMALE NUT	COPPER ALLOY	NICKEL PLATED
8	FEMALE HOUSING	NYLON	BLACK
9	FEMALE CONTACT	COPPER ALLOY	FLASH GOLD



NOTE:

①. TECHNICAL DATA: SEE TABLE 1

②. CODE POSITION INDICATOR

③. RECOMMENDED TORQUE 0.6 Nm

④. -*:CABLE LENGTH
-0.5:0.5M,
-1.0:1.0M,
-1.5:1.5M,
-3.0:3.0M,
-5.0:5.0M,
-7.0:7.0M,
-10.0:10.0M,

5. CABLE ASSEMBLY TO BE PACKAGED IN POLYBAGS

⑥. LABEL CONTAINS: PN, DATE CODE...

⑦. -00X:FOR CABLE LENGTH , SEE TABLE 1 AND REFER TO LENGH"L".

注释:

①. 技术参数:参考表1

②. CODE位置指示

③. 推荐扭矩0.6 Nm

④. -*:线缆长度
-0.5:0.5M,
-1.0:1.0M,
-1.5:1.5M,
-3.0:3.0M,
-5.0:5.0M,
-7.0:7.0M,
-10.0:10.0M,

5. 线缆组件塑料袋包装

⑥. 标签包含: 产品编号, 日期代码...

⑦. -00X:线缆长度,参考表2,参照长度"L"

TABLE 1: TECHNICAL DATA	T41521X3002-00X	T41521X3003-00X	T41521X3004-00X	T41521X3005-00X
RATED VOLTAGE	250V			60V
RATED IMPULSE VOLTAGE	2500V			1500V
RATED CURRENT	4A			
POLLUTION DEGREE	3			
OVERVOLTAGE CATEGORY	II			
MATERIAL GROUP	II			
DEGREE OF PROTECTION	IP67			

WIRES: 0.34mm ² (22AWG) WIRE COLOR: WH/BR/BK/BL/GR OD: APPROX.4.5MM FOR 2P/3P APPROX.5.0MM FOR 4P/5P	STANDARD: -001:0.5 M -002:1.0 M -003:1.5 M -004:3.0 M -005:5.0 M -006:7.0 M -007:10.0 M CUSTOMIZATION: -**0:**.0 M -**5:**.5 M	FIXED: -10°C~+80°C FLXIBLE: -5°C~+80°C	GRAY	PVC (UL)	RPC-M12-5MS-**-△-M12-5FS-PVC1	5	T4152173005-00X△
					RPC-M12-4MS-**-△-M12-4FS-PVC1	4	T4152173004-00X△
					RPC-M12-3MS-**-△-M12-3FS-PVC1	3	T4152173003-00X△
					RPC-M12-2MS-**-△-M12-2FS-PVC1	2	T4152173002-00X△
		FIXED: -40°C~+80°C FLXIBLE: -25°C~+80°C	YELLOW	PUR(UL)	RPC-M12-3MS-**-△-M12-3FS-PUR2	3	T4152183003-00X△
			GRAY	PUR (UL)	RPC-M12-5MS-**-△-M12-5FS-PUR	5	T4152123005-00X△
					RPC-M12-4MS-**-△-M12-4FS-PUR	4	T4152123004-00X△
					RPC-M12-3MS-**-△-M12-3FS-PUR	3	T4152123003-00X△
					RPC-M12-2MS-**-△-M12-2FS-PUR	2	T4152123002-00X△
		FIXED: -10°C~+80°C FLXIBLE: -5°C~+80°C	BLACK	PVC (UL)	RPC-M12-5MS-**-△-M12-5FS-PVC	5	T4152113005-00X△
					RPC-M12-4MS-**-△-M12-4FS-PVC	4	T4152113004-00X△
					RPC-M12-3MS-**-△-M12-3FS-PVC	3	T4152113003-00X△
RPC-M12-2MS-**-△-M12-2FS-PVC	2				T4152113002-00X△		
CABLE CHARACTERISTIC	LENGTH "L"	CABLE TEMP. RANGE	JACKET COLOR	JACKET MATERIAL	TYPE	POS.	TE PN SEE LENGTH "L"

PIN ARRANGEMENT A-CODE			
T41521X3002-00X	T41521X3003-00X	T41521X3004-00X	T41521X3005-00X

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4152123005-002](#)