



- △ -T- 面より2mmの範囲で測定
- △ THESE DIMENSIONS TO BE MEASURED BETWEEN -T- AND 2.0.
- 2. 適合する相手ハラソング型番は172021, 172054, 172852, 172054.
- 2. MATABLE PLUG HOUSING : 172021, 172245, 172852, 172854.
- 3. 適用製品規格 NO. 108-5124.
- 3. PRODUCT SPECIFICATION : 108-5124.
- △ 推奨取付ねじ : JIS B1115, B1122 タッピンねじ
- △ RECOMMENDED MOUNTING SCREW : JIS B1115 OR B1122
- △ PAN HEAD TAPPING SCREW, CLASS 3, DIAMETER 2, LENGTH 5.

SELECTIVE-TIN	PRE-TIN	BLACK	172256-2
SELECTIVE-TIN (MATE)	SELECTIVE-TIN (BRIGHT)	BLACK	172256-1
SOLDERING SIDE	CONTACT SIDE	COLOR	PART NUMBER
※田付の側	※接触側	色	製品型番
CONTACT FINISH		CONTACT FINISH	
コンタクト仕上		コンタクト仕上	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 特 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0	PLC	±
1	PLC	±
2	PLC	±
3	PLC	±
4	PLC	±
ANGLES		
		±

MATERIAL: HOUSING : 66NYLON CONTACT : COPPER ALLOY

FINISH: SEE TABLE

WEIGHT: CUSTOMER DRAWING

DMN: T. SHINOHARA

CHK: K. BETSUI

APVD: K. BETSUI

NAME: tyco Escorts

28 POSITION CAP HOUSING ASSEMBLY (VERTICAL TYPE)

DUAL LINE INTERLOCK CONNECTOR

SIZE: A3

CAGE CODE: 00779

DRAWING NO: 172256

SCALE: 2:1

SHEET: 1 OF 1

REV: E1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[172256-1](#)