

| APPLICATOR PARTS LIST | | | | TYPE | | | AMP INCORPORATED HARRISBURG, PENNA. | | | |
|-----------------------|--------------------------|------|----------|----------------------|-----------------------------|----------|-------------------------------------|-----------------------------|--------------|-----------|
| | | | | SIDEWISE | | | | | | |
| NO. | DESCRIPTION | REQ. | PART NO. | NO. | DESCRIPTION | REQ. | PART NO. | CRIMPING DATA | | TERMINALS |
| 1 | WIRE CRIMPER 453933-7 | 1 | 453933-7 | 42 | Shear Plate - Left | 1 | 811855-1 | TO APPLY TERMINAL | | 66113- |
| 2 | INS. CRIMPER | 1 | 465603-2 | 43 | Shear Block - Right | 1 | 386372 | WIRE SIZE | CRIMP HEIGHT | |
| 3 | ANVIL | 1 | 465998-1 | 44 | Floating Shear | 1 | 465406 | 26 | | |
| 4 | ANVIL SPACER | 1 | 810070-4 | 45 | Retaining Plate - Front | 1 | 811714-3 | | 037 | |
| 5 | SHEAR BLADE | | | 46 | Retaining Plate - Rear | 1 | 810822-1 | 22 | | |
| 6 | REAR SHEAR PLATE | | | 47 | Spring - Shear Return | 1 | 374322 | | | |
| 7 | REAR ANVIL SPACER PLATE | 1 | 811959-1 | 48 | Shear Depressor 453302-1 | 1 | 382265-7 | | | |
| 8 | FRONT SHEAR PLATE | | | 49 | Key - Shear Retainer | 1 | 386358 | CRIMP | SIZE | TYPE |
| 9 | REAR ANVIL SPACER PLT. | | | 50 | Guard Mount | 1 | 811986-1 | WIRE | .062 | "5" |
| 10 | FRONT ANVIL SPACER BLOCK | 1 | 810799-2 | 51 | Punch Holder | 1 | 810498-3 | INSUL. | .070 | "0" |
| 11 | TOOL SPACER | 1 | 370695 | 52 | Punch ASSY. | 1 | 810738-1 | SLEEVED | | .300 |
| 12 | CRIMP SPACER | 1 | 375548 | 53 | | | | INSULATION RANGE | WIRE RANGE | |
| 13 | FRONT STRIP GUIDE | 1 | 810971-2 | 54 | | | | .053 Max. | 26 - 22 | |
| 14 | REAR STRIP GUIDE | 1 | 465413-1 | 55 | | | | EXPLODED VIEW | | |
| 15 | RAM | 1 | 471912 | 56 | | | | A-6002-4 A-6002-6 | | |
| 16 | TOOL HOLDER | | | 57 | | | | REMARKS: | | |
| 17 | ADJ. CRIMP MOUNT ASSY. | 1 | 465392-9 | 58 | | | | Max. Ins. Crimp Height .060 | | |
| 18 | ADJ. BLOCK | | | 59 | | | | △ Mounts on top of item #13 | | |
| 19 | APPLICATOR MOUNT ASSY. | | | 60 | | | | | | |
| 20 | BASE PLATE | 1 | 465100 | 61 | | | | | | |
| 21 | BASE BLOCK | 1 | 465101 | 62 | | | | | | |
| 22 | STRIP GUIDE PLATE | 1 | 465414-1 | 63 | | | | | | |
| 23 | ANVIL HOLDER | | | 64 | Paper Separator | 1 | 694927-1 | | | |
| 24 | WIRE STOP | 1 | 811787-1 | 65 | TENSION ADJ. PLATE | 1 | 374999 | | | |
| 25 | STRIPPER - Wire Stop | 1 | 386361 | 66 | 2 Ft. Dia. Reel Spind Assy. | 1 | 453596-4 | | | |
| 26 | STRIPPER MOUNT | 1 | 386362 | 67 | Air Feed Assy. | 1 | 690021- | | | |
| 27 | RETAINER PLATE | 1 | 389078 | 68 | Lubricator Assy. | 1 | 465181-2 | | | |
| 28 | STRIPPER MOUNT BRACKET | 1 | 387715-1 | 69 | SYNTHETIC OIL | 1 | 22014-1 | | | |
| 29 | STRIPPER BUSHING | 1 | 386368 | 70 | | | | | | |
| 30 | STOCK DRAG | 1 | 386955 | 71 | | | | | | |
| 31 | STOCK DRAG HANDLE | | | 72 | | | | | | |
| 32 | STOCK DRAG STUD | 1 | 374900 | REV. REVISION RECORD | | DATE | BY | ECN | | |
| 33 | STOCK DRAG SPRING | 1 | 370572 | B | Change Item 42 44 45 | 11-11-65 | | | | |
| 34 | STOCK DRAG ADJ. NUT | 1 | 21022-3 | C | ITEM 32 WAS -2 | 12/1/65 | | | | |
| 35 | FEED FINGER HOLDER | 1 | 386912 | D | ADD ITEM 38 | 12-20-66 | | L-4323 | | |
| 36 | FEED FINGER | 1 | 386911 | E | ITEM 7 WAS -2 | 5-8-69 | | L-6617 | | |
| 37 | FEED FINGER TIP | 1 | 387251 | F | ADDED ITEM 65 374999 | 5-27-69 | | L-6693 | | |
| 38 | FEED FINGER GUIDE | 1 | 689915-2 | G | REV. PER ECN | 9-9-69 | | L-6952 | | |
| 39 | BASE CASTING | 1 | 570238 | H | REV PER ECN | 6-4-71 | | L-8332 | | |
| 40 | GUARD 460881-2 | 1 | 460881-2 | I | REV PER ECN | 4/31/71 | | L-8362 | | |
| 41 | BRACKET | 1 | 811304-1 | | | | | | | |

**— IMAGINE —
FOR REPLACEMENT KEY**

■ DENOTES WEARING PARTS
RECOMMEND PURCHASE REPLACEMENT

THIS APPLICATOR IS TO BE USED ON
AMP-O-ELECTRIC 1-471273-2
AIR FEED

SERIAL NO. _____ DATE SHIPPED _____ DESIGNED _____
CUSTOMER NAME AND ADDRESS _____ CHK'D _____
APPLICATOR NUMBER _____ REV. M 670892-3 SHEET 1 OF 31

M REV ITEM 40 11-10-78 R275Z
 K 48 WAS 378265-7-78 7-35-71 R275Z L-8359
 L REV PER ECN 4-5-73 TK - L-9645 FOR HARDWARE SEE 1-687511-5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[670892-3](#)