


NUMBER C-176285



METRIC

ALL DIMENSIONS IN MM. DO NOT SCALE PRINT

PRINT DIST



- 備:
1. 適用製品規格: 108-5302
  2. 適用コンタクト型番  
プラグ・コンタクト: 175150-□(φ20-φ16AWG)  
175149-□(φ26-φ22AWG)
  3. 取替相手側製品型番  
プラグ・ハウジング: 176274-□  
リセ・コンタクト: 175152-□(φ20-φ16AWG)  
175151-□(φ26-φ22AWG)
  4. 取扱説明書: IS-503J

- NOTES:
1. PRODUCT SPEC.: 108-5302
  2. APPLICABEL CONTACT P/N  
TAB CONTACT: 175150-□(φ20-φ16AWG)  
175149-□(φ26-φ22AWG)
  3. MATING CONN, P/N  
PLUG HSG: 176274-□  
REC CONTACT: 175152-□(φ20-φ16AWG)  
175151-□(φ26-φ22AWG)
  4. INSTRUCTION SHEET: IS-503J

断面 "A"- "A"  
(SECT)

5. APPLICATION SPEC: 114-5142

黒 (BLACK)	6	176285-9
青 (BLUE)	↑	↑ -6
黄 (YELLOW)	↑	↑ -4
赤 (RED)	↓	↓ -2
自然色 (NATURAL)	6	176285-1
ハウジング色調 (HOUSING COLOR)	極数 (Pos.)	型番 (P/N)

© 19 BY AMP (Japan) LTD.				Tyco Electronics AMP K.K. Kawasaki, Japan	
適合電線範囲 (WIRE RANGE) mm <sup>2</sup> (AWG)		絶縁外皮径 (INSULATION DIA.) mm		名称 (NAME) AMPユニバーサルパワーコネクタ 6極 3.95mmピッチキャップ・ハウジング (2列タイプ) AMP UNIVERSAL POWER CONN. 3.95mm PITCH CAP HOUSING 6 Pos (2BL ROW)	
材料 (MATERIAL) S/S ナイロン (UL54V-0) S/S NYLON (UL54V-0)		仕上 (FINISH)		寸法 (DIMENSIONS) 102mm <sup>2</sup> : φ0.2 108mm <sup>2</sup> : φ0.25 208mm <sup>2</sup> : φ0.3 φ: φ3°	
改訂 FJ00-0836-02 K.K. MS 4/15/02		改訂 EJ-12183 Y.N.MS 1/14/00		改訂 EJ-12119 M.S.Y.F. 10/15/99	
DR. Y. NARISAWA 11/19		DE. M. Shide 1/19/00		APP. J. Ogasawara 1/19/00	
LTR 変更 (REVISION RECORD)		DR CHK DATE		SIZE LOC 符号 (No.) A3 J C-176285 尺度 (SCALE) REV. D SHEET 1 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[176285-2](#)