




| LOC | DIST | REVISIONS | | | | |
|-----|------|-----------|-----|--------------------------------|---------|-------|
| DF | A0 | P | LTR | DESCRIPTION | DATE | APVD |
| | | B | | REV & REDRAWN PER ECO 06-03778 | 8-10-06 | CT DE |



1 FINISH: ELECTROLESS NICKEL.
2 FINISH: BLUE ANODIZED.

| | | | |
|-------------|--------|----------------|----------|
| .235 [5.97] | 1 | ALUMINUM ALLOY | 207885-6 |
| .235 [5.97] | 2 | ALUMINUM ALLOY | 207885-5 |
| .390 [9.91] | 1 | ALUMINUM ALLOY | 207885-3 |
| .390 [9.91] | 2 | ALUMINUM ALLOY | 207885-2 |
| DIM A | FINISH | MATERIAL | PART NO. |

| | | | | | | |
|--|---|------------------|---------|--|-----|------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN | 8-10-06 | AMP Tyco Electronics Corporation Harrisburg, PA 17105-3608 | | |
| | | CHK | 8-11-06 | | | |
| DIMENSIONS: INCHES [mm] | | D.EABY | 8-11-06 | NAME STAMPED GROMMET PROTECTOR,UNIVERSAL | | |
| | | APVD | 8-11-06 | | | |
| | TOLERANCES UNLESS OTHERWISE SPECIFIED: | PRODUCT SPEC | | SIZE A2 | | |
| | 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .010 [0.25] 4 PLC ± - ANGLES ± - | APPLICATION SPEC | | | | |
| MATERIAL SEE TABLE | | FINISH | | CAGE CODE 00779 | | DRAWING NO C=207885 |
| | | SEE TABLE | | | | |
| CUSTOMER DRAWING | | | | WEIGHT | - | RESTRICTED TO - |
| | | | | SCALE | 3:1 | SHEET 1 of 1 |
| | | | | REV | B | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[207885-3](#)