




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	REVISED	07NOV2016	ERL	ERL
	D	REVISED	15MAY2019	JAB	NE
	D1	REVISED PER ECO-19-011159	17JUL2019	KF	NE
	D2	REVISED PER ECN-21-125134	05NOV2021	CN	AC



	2.13	2.28	1.00		RG-58 LL	4-2203270-7	1-2203270-9
	2.13	2.28	1.00		RG-58, DACAR 037	-	1-2203270-8
	2.13	2.28	1.00		RG-58, DACAR 037	-	1-2203270-7
	2.13	2.28	1.00		RG-58 LL	3-2203270-2	1-2203270-5
	1.89	2.03	0.85		RTK-031, 2DS-PPFW(TA), RTK044	2-2203270-6	1-2203270-4
OBSOLETE	-	-	-	-	-	-	1-2203270-3
	1.42	1.57	0.55		1.5DS, DACAR 363, DACAR 462, RG-174, RG-174 LL, RG-316	2-2203270-3	1-2203270-2
	1.05	1.14	0.35		1.5CS	2-2203270-9	1-2203270-1
1-2203270-9	-	-	-	-	-	-	1-2203270-0
	1.89	2.03	0.85		RTK-031, 2DS-PPFW(TA), RTK044	4-2203270-5	2203270-8
OBSOLETE	-	-	-	-	-	-	2203270-6
	1.42	1.57	0.55		1.5DS, DACAR 363, DACAR 462, RG-174, RG-174 LL, RG-316	4-2203270-3	2203270-4
	1.05	1.14	0.35		1.5CS	-	2203270-2
	C	B	A	FINISH	APPLICABLE CABLE SIZE	ALTERNATE PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. J. HARDY	12AUG2015		TE Connectivity	
		CHK D. J. LANE	12AUG2015			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. J. LANE	12AUG2015		NAME CENTER CONTACT, FEMALE, 180 DEGREE, FAKRA AUTOMATED	
	0 PLC ± 1 PLC ± 2 PLC ±0.05 3 PLC ± 4 PLC ± ANGLES ±	PRODUCT SPEC 108-32107				
MATERIAL	FINISH	APPLICATION SPEC 114-32145	SIZE A2	CAGE CODE -	DRAWING NO C-2203270	RESTRICTED TO
	SEE TABLE	WEIGHT -			SHEET 10 of 1	REV D2
CUSTOMER DRAWING			SCALE			

- | | |
|---|---|
|  | PHOSPHOR BRONZE.
ALTERNATE: COPPER ALLOY. |
|  | 0.38 μ m MIN GOLD PLATE IN LOCALIZED GOLD PLATE AREA,
2.5 μ m MIN TIN PLATE IN LOCALIZED TIN PLATE AREA,
BOTH OVER 1.5 μ m MIN NICKEL PLATE. |
|  | 0.80 μ m MIN GOLD PLATE IN LOCALIZED GOLD PLATE AREA,
2.5 μ m MIN TIN PLATE IN LOCALIZED TIN PLATE AREA,
BOTH OVER 1.27 μ m MIN NICKEL PLATE. |

4. CENTER CONTACT WILL ACCEPT COAXIAL CABLE: SEE TABLE.
5. 2203270-8 AS SHOWN.
6. PACKAGED ON REEL.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2203270-9](#)