







P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	08MAY2020	M. J	E. I



- 1 CONTACT POINT TO HDR CONNECTOR : GOLD PLATING UNDER Ni PLATING
- 2 CONTACT POINT TO WIRE : TIN PLATING UNDER Ni PLATING



P/N		
6-2260663-1	4-2260663-2	4-2260663-1
6	4	4
6	4	4
1		
	1	1
1		
	1	
		1
QTY	FINISH	

	STAINLESS STEEL			SPRING	⑥
12	COPPER ALLOY			REC CONTACT	⑤
	THERMO PLASTIC, POLYESTER (UL94V-0),COLOR:BLACK		6	COVER HOUSING	④
			4		③
	THERMO PLASTIC, POLYESTER (UL94V-0),COLOR:BLACK	X	6	HOUSING	②
	THERMO PLASTIC, POLYESTER (UL94V-0),COLOR:BLACK	Y	4	HOUSING	①
		X	4		①
FINISH	MATERIAL	KEY	POS	NAME	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.3

1 PLC ±0.3

2 PLC ±0.3

3 PLC ±0.3

4 PLC ±0.3

ANGLES ±3°

FINISH
SEE TABLE

DWN
M. JIANG
08MAY2020

CHK
T. SHIMOYASU
08MAY2020

APVD
E. IKEMATSU
08MAY2020

PRODUCT SPEC
108-140022

APPLICATION SPEC
408-78067

WEIGHT
-

CUSTOMER DRAWING

SCALE
1:1

SHEET
1 OF 4

REV
A

NAME
DYNAMIC D5900
RECEPTACLE ASSY

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2260663







RESTRICTED TO
-

TE Connectivity

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

COMPANY LOGO


KEY CODE




DATE CODE

CAVITY MARK

CIRCUIT NO.









4-2260663-1 (4POS KEY:X)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. JIANG 08MAY2020		 TE Connectivity													
DIMENSIONS: mm		CHK T. SHIMOYASU 08MAY2020															
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD F. IKEMATSU 08MAY2020		NAME DYNAMIC D5900 RECEPTACLE ASSY											
		PRODUCT SPEC 108-140022		SIZE A3						CAGE CODE 00779		DRAWING NO C-2260663		RESTRICTED TO -			
		APPLICATION SPEC 408-78067															
		MATERIAL SEE SHEET 1		FINISH SEE SHEET 1		WEIGHT -		SCALE 1:1						SHEET 2 OF 4		REV A	
CUSTOMER DRAWING																	

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

COMPANY LOGO

KEY CODE




REFER TO SHEET2 FOR THE DIMENSIONS WHICH ARE NOT INDICATED ON THIS SHEET.

4-2260663-2(4POS KEY:Y)

DATE CODE

CAVITY MARK

CIRCUIT NO.








THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. JIANG 08MAY2020	 TE Connectivity		
		CHK T. SHIMOYASU 08MAY2020			
		APVD F. IKEMATSU 08MAY2020	NAME DYNAMIC D5900 RECEPTACLE ASSY		
DIMENSIONS: mm		PRODUCT SPEC 108-140022			
		APPLICATION SPEC 408-78067			
		WEIGHT -	SIZE A3	CAGE CODE 00779	RESTRICTED TO -
MATERIAL SEE SHEET 1		FINISH SEE SHEET 1	DRAWING NO C-2260663	SCALE 1:1	REV A
		CUSTOMER DRAWING	SHEET 3	OF 4	

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


COMPANY LOGO

KEY CODE




DATE CODE

CIRCUIT NO.



6-2260663-1 (6POS KEY:X)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. JIANG 08MAY2020	 TE Connectivity		
DIMENSIONS: mm		CHK T. SHIMOYASU 08MAY2020			
		APVD F. IKEMATSU 08MAY2020	NAME DYNAMIC D5900 RECEPTACLE ASSY		
		PRODUCT SPEC 108-140022	SIZE A300779		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 408-78067	CAGE CODE C-2260663		DRAWING NO
MATERIAL SEE SHEET 1		WEIGHT -	RESTRICTED TO -		
FINISH SEE SHEET 1		CUSTOMER DRAWING		SCALE 1:1	SHEET 4 OF 4
				REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2260663-1](#)