


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	19JAN2022	SCB	PS



NOTES:

- 1 MATERIALS & FINISH
HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN
PUSH BUTTON : PA66, UL94 V0, COLOR - ORANGE
CONTACT : COPPER ALLOY, TIN PLATED
SPRING : STAINLESS STEEL
2. MECHANICAL
WIRE STRIPPING LENGTH : 11 - 12 mm
3. ELECTRICAL
WIRE RANGE : 12 - 26 AWG
RATED VOLTAGE : 300V
RATED CURRENT : 10A (UG D)
: 16A (UG B)
INSULATION RESISTANCE : >2000 M Ohm (500V DC)
4. OPERATING TEMPERATURE RANGE : -40°C TO +105°C
- 5 TOLERANCE NOT CUMULATIVE

81.90	16	1-2385007-6
76.82	15	1-2385007-5
71.74	14	1-2385007-4
66.66	13	1-2385007-3
61.58	12	1-2385007-2
56.50	11	1-2385007-1
51.42	10	1-2385007-0
46.34	9	2385007-9
41.26	8	2385007-8
36.18	7	2385007-7
31.10	6	2385007-6
26.02	5	2385007-5
20.94	4	2385007-4
15.86	3	2385007-3
10.78	2	2385007-2
DIM A	NO. OF POS	TE PN




2385007-3 AS SHOWN



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

- 0 PLC ±
- 1 PLC ±
- 2 PLC ±
- 3 PLC ±
- 4 PLC ±
- ANGLES ±

FINISH



DWN	12JAN2022
CHK	SHRICHARANA B
CHK	SUBHASREE S
APVD	12JAN2022
PRASHANTH S	
PRODUCT SPEC	108-32299
APPLICATION SPEC	114-32242
WEIGHT	-

CUSTOMER DRAWING

NAME
TERMINAL BLOCK, SPRING PLUG
PITCH 5.08mm

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	©=2385007	-

SCALE	SHEET	OF	REV
4:1	1	1	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2385007-2](#)