


| REVISIONS | | | | |
|-----------|-----|---------------------------|-----------|-------|
| P | LTR | DESCRIPTION | DATE | APP'D |
| G | | REVISED PER ECO-21-005294 | 07MAY2021 | KK AK |



1. CHARACTERISTIC IMPEDANCE: 100±10 OHMS (MEASURED DIFFERENTIALLY)

2 LABEL INFORMATION FOR 25 GIG PNS (-1 THRU -8): -1 SHOWN



3. SEE SHEET 2 FOR WIRING SCHEMATIC.

4. ROHS COMPLIANCE: PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE CONNECTIVITY SPECIFICATION TEC-138-702.

5 TEST IN ACCORDANCE WITH IEEE802.3by.

6 DASH NUMBER 41 THRU 45 CONFORM TO 56G, PAM-4 IEEE802.3CD PERFORMANCE REQUIREMENTS.

7 LABEL INFORMATION FOR 56 GIG PNS (-41 THRU -45): -41 SHOWN




| | | | | |
|----------|-----------|------|-----------|-------------|
| 6 | 26 | 3000 | +80 -0 | 4-2821224-5 |
| | 26 | 2500 | +80 -0 | 4-2821224-4 |
| | 26 | 2000 | +80 -0 | 4-2821224-3 |
| | 26 | 1500 | +80 -0 | 4-2821224-2 |
| | 26 | 1000 | +50 -0 | 4-2821224-1 |
| 5 | 26 | 5000 | +80 -0 | 2821224-8 |
| | 26 | 4000 | +80 -0 | 2821224-7 |
| | 26 | 3500 | +80 -0 | 2821224-6 |
| | 26 | 3000 | +80 -0 | 2821224-5 |
| | 26 | 2500 | +80 -0 | 2821224-4 |
| | 26 | 2000 | +80 -0 | 2821224-3 |
| | 26 | 1500 | +80 -0 | 2821224-2 |
| | 26 | 1000 | +50 -0 | 2821224-1 |
| STANDARD | WIRE GAGE | L | PART NO | |

THIS DRAWING IS A CONTROLLED DOCUMENT.

| | | | |
|------------------|--|---------------------------|--|
| DIMENSIONS: mm | TOLERANCES UNLESS OTHERWISE SPECIFIED: | DIN T. SMITH 08OCT2015 | STE TE Connectivity Ltd. |
| 0. PLC ± | 1. PLC ± | CHK C. POGASH 08OCT2015 | NAME CABLE ASSY, 26 AWG, SFP+ TO SFP+, 28GIG |
| 2. PLC ± | 3. PLC ± | APP'D G. POGASH 08OCT2015 | PRODUCT SPEC |
| 4. PLC ± | ANGLES ± | APPLICATION SPEC | RESTRICTED TO |
| MATERIAL | FINISH | SIZE A1 | WEIGHT 0 |
| CUSTOMER DRAWING | | SCALE 1:1 | SHEET 1 OF 2 |

| REVISIONS | | | | |
|-----------|-----------|-------------|----|-------|
| REV | DATE | DESCRIPTION | BY | APP'D |
| 1 | 08OCT2015 | SEE SHEET 1 | - | - |



| | | | | | |
|--|--|--------------------------|--|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DIN T.SMITH 08OCT2015 | | TE Connectivity Ltd. | |
| DIMENSIONS: mm | | CHK C.POGASH 08OCT2015 | | NAME CABLE ASSY,26 AWG,SFP+ TO SFP+, 28GIG | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APP'D C.POGASH 08OCT2015 | | RESTRICTED TO | |
| 0. PLC ± - | | PRODUCT SPEC | | SIZE A1 | |
| 1. PLC ± - | | APPLICATION SPEC | | CAGE CODE 00779 | |
| 2. PLC ± - | | WEIGHT | | DRAWING NO. 2821224 | |
| 3. PLC ± - | | MATERIAL | | SCALE 1:1 | |
| 4. PLC ± - | | FINISH | | SHEET 2 OF 2 | |
| ANGLES ± - | | CUSTOMER DRAWING | | REV G | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2821224-2](#)