



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT 2016 TE CONNECTIVITY ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-		SEE SHEET 1	-	-

48	52	50
42	46	44
38	42	40
30	34	32
28	32	30
26	30	28
24	28	26
22	26	24
20	24	22
18	22	20
16	20	18
14	18	16
12	16	14
10	14	12
8	12	10
6	10	8
4	8	6
2	6	4
DIM "F"	DIM "E"	POSITION PER CONNECTOR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11FEB2016 RAKSHITH NAYAK	 TE Connectivity	
		CHK 01APR2016 KARTHIK J K		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.1 2 PLC ±0.05 3 PLC ± 4 PLC ±		APVD 01APR2016 PRASHANTH S
		PRODUCT SPEC 108-64040		NAME AMPMODU 2mm SHROUDED HEADER, DUAL ROW, RIGHT ANGLE
MATERIAL SEE NOTES		FINISH SEE NOTES		APPLICATION SPEC 114-64040
		WEIGHT -		SIZE A2
		CUSTOMER DRAWING		CAGE CODE 00779
		SCALE 6:1		DRAWING NO C-2823351
		SHEET 2 OF 3		RESTRICTED TO -
				REV A3

Printed on 18 Oct 2021 15:05 (India Standard Time) from TE454782

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT 2016 TE CONNECTIVITY ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-		SEE SHEET 1	-	-

SMART PART NUMBER
 2MM - HSD - D - HT - - - - -

PRODUCT SERIES

2MM AMPMODU 2mm series

GENDER / TYPE

HSD Shrouded headers for detent latch

NUMBER OF ROWS

D Double row

NUMBER OF PINS PER ROW

XX 02 through 16,20,22,25 (enter two digits)

ORIENTATION & TERMINATION

HT Horizontal through hole

PACKAGING

TB	Tube without cap	
TBP	Tube with cap	8
TRP	Tape and reel with cap	8
BX	Box	9

PLATING

T	Tin
F	0.1µm Gold (Gold flash)
M	0.38µm Gold
H	0.76µm Gold

TAIL LENGTH


01	2.2 mm
02	2.8 mm
03	3.4 mm

SMART PN EXAMPLES :

1. AMPMODU 2MM, SHROUDED HEADER STD VERSION, DOUBLE ROW, 02 POSITION PER ROW, RIGHT ANGLE MOUNT, 2.2MM SOLDER TAIL LENGTH, TIN PLATING, TUBE W/O CAP
2MM-HSD-D02-HT-01-T-TB
2. AMPMODU 2MM, SHROUDED HEADER STD VERSION, DOUBLE ROW, 25 POSITION PER ROW, RIGHT ANGLE MOUNT, 3.4MM SOLDER TAIL LENGTH, 0.76µm GOLD PLATING, BOX PACKAGING
2MM-HSD-D25-HT-03-H-BX

THIS PRINT IS
PRELIMINARY
 UNQUALIFIED PRODUCT
 CONTACT PRODUCT ENGINEERING
 BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAKSHITH NAYAK 11FEB2016
DIMENSIONS: mm		CHK KARTHIK J K 01APR2016
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD PRASHANTH S 01APR2016
0 PLC ±	1 PLC ±0.1	PRODUCT SPEC 108-64040
2 PLC ±0.05	3 PLC ±	APPLICATION SPEC 114-64040
4 PLC ±	ANGLES ±2°	WEIGHT -
MATERIAL SEE NOTES	FINISH SEE NOTES	CUSTOMER DRAWING

 TE Connectivity		NAME AMPMODU 2mm SHROUDED HEADER, DUAL ROW, RIGHT ANGLE	
		SIZE A2	CAGE CODE 00779
DRAWING NO C=2823351		RESTRICTED TO -	
SCALE 1:1		SHEET 3 OF 3	
REV A3			

Printed on 18 Oct 2021 15:05 (India Standard Time) from TE454782

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2823355-4](#)