





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G5	REVISED PER ECN-22-150900	27APR2022	RK	CSD

AMP WIRE RANGE	 E13288 Listed
1/0 AWG SOLID OR STRANDED	1/0 AWG STRANDED

 LR7189 Certified
1/0 AWG SOLID OR STRANDED

- 1 TIN PL 0.00254[.000100] MIN EXT. THK PER ASTM B-545
- 2 NOTE DELETED

50	LOOSE PIECE	CLEANED	COPPER ASTM B-152 1.778±0.076[.070±.003] ANNEALED	2-321868-2
50	LOOSE PIECE	1		321868
QTY.	PACKAGE TYPE	FINISH	MATERIAL	PART NUMBER

MAX RECOMMENDED OPERATING TEMPERATURE: 170°[338°F]C	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 8/30/91	 TE Connectivity				
			CHK RD HEIM 9/30/91					
VOLTAGE RATING: N/A	DIMENSIONS: mm[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD AJ KAUFMAN 9/30/91	NAME TERMINAL, RING TONGUE, SOLISTRAND WIRE SIZE 50.0mm2 [1/0] AWG			
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -		PRODUCT SPEC UL 486 A-B				
CIRCULAR MIL AREA: 42.4–60.6mm² [83,700–119,500] SOILD OR STRANDED	MATERIAL SEE TABLE	FINISH SEE TABLE		APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				WEIGHT —	A3	00779	C-321868	—
				CUSTOMER DRAWING				SCALE 2:1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[321868](#)