




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	K3	REVISED PER ECN-22-156403	03JUN2022	RK	CSD



- 1 TONGUE MATERIAL THK: 1.02±0.05[.040±.002]
- 2 FOR 3.81[.150] TO 5.84[.230] WIRE INSULATION DIA
- 3 APPLIES FROM THE METAL EDGE OF THE BARREL TO THE CENTER OF THE STUD
- 4 MEETS MS17143-18, CLASS 1

OBSOLETE	1	2-327966-1 ON TAPE	BODY & SLEEVE: COPPER (ASTM-B152) TIN PL (ASTM-B545) INSULATION: NYLON (ASTM-D4066) TYPE 1, COLOR: YELLOW	2-327966-3
OBSOLETE	1	WIRE TERMINAL		2-327966-1
OBSOLETE	1	327966 ON TAPE	BODY: COPPER (ASTM-B152) TIN PL (ASTM-B545) SLEEVE: COPPER (ASTM-B152) INSULATION: NYLON COLOR: YELLOW	2-327966-2
	1	WIRE TERMINAL		4 327966
QTY		DESCRIPTION	MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 02SEP09	 TE Connectivity			
		CHK JEFF RUTH 02SEP09				
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD TOM MICHELUTTI 02SEP09	NAME TERMINAL PIDG – RECTANGULAR TONGUE WIRE SIZE: 12–10			
	0 PLC ± – 1 PLC ± – 2 PLC ± – 3 PLC ± 0.20 [.008] 4 PLC ± – ANGLES ± 5°	PRODUCT SPEC —				
		APPLICATION SPEC —				
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-327966	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV K3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[327966](#)