

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C

C

B

B



A

A

	99.06[3.900]	101.60[4.000]	80		9-535542-0
	96.52[3.800]	99.06[3.900]	78		8-535542-9
	93.98[3.700]	96.52[3.800]	76		8-535542-8
	91.44[3.600]	93.98[3.700]	74		8-535542-7
	88.90[3.500]	91.44[3.600]	72		8-535542-6
	86.36[3.400]	88.90[3.500]	70		8-535542-5
	83.82[3.300]	86.36[3.400]	68		8-535542-4
	81.28[3.200]	83.82[3.300]	66		8-535542-3
	78.74[3.100]	81.28[3.200]	64		8-535542-2
	76.20[3.000]	78.74[3.100]	62		8-535542-1
	73.66[2.900]	76.20[3.000]	60		8-535542-0
	71.12[2.800]	73.66[2.900]	58		7-535542-9
	68.58[2.700]	71.12[2.800]	56		7-535542-8
	66.04[2.600]	68.58[2.700]	54		7-535542-7
	63.50[2.500]	66.04[2.600]	52		7-535542-6
	60.96[2.400]	63.50[2.500]	50		7-535542-5
	58.42[2.300]	60.96[2.400]	48		7-535542-4
	55.88[2.200]	58.42[2.300]	46		7-535542-3
	53.34[2.100]	55.88[2.200]	44		7-535542-2
	50.80[2.000]	53.34[2.100]	42		7-535542-1
	48.26[1.900]	50.80[2.000]	40		7-535542-0
	45.72[1.800]	48.26[1.900]	38		6-535542-9
	43.18[1.700]	45.72[1.800]	36		6-535542-8
	40.64[1.600]	43.18[1.700]	34		6-535542-7
	38.10[1.500]	40.64[1.600]	32		6-535542-6
	35.56[1.400]	38.10[1.500]	30		6-535542-5
	33.02[1.300]	35.56[1.400]	28		6-535542-4
	30.48[1.200]	33.02[1.300]	26		6-535542-3
	27.94[1.100]	30.48[1.200]	24		6-535542-2
	25.40[1.000]	27.94[1.100]	22		6-535542-1
	22.86[.900]	25.40[1.000]	20		6-535542-0
	20.32[.800]	22.86[.900]	18		5-535542-9
	17.78[.700]	20.32[.800]	16		5-535542-8
	15.24[.600]	17.78[.700]	14		5-535542-7
	12.70[.500]	15.24[.600]	12		5-535542-6
		10.16[.400]	10		5-535542-5
		7.62[.300]	8		5-535542-4
		5.08[.200]	6		5-535542-3
		2.54[.100]	4		5-535542-2
		-	2		5-535542-1
FINISH	B	A	NO OF POSN	PART NUMBER	

	99.06[3.900]	101.60[4.000]	80	4-535542-0
	96.52[3.800]	99.06[3.900]	78	3-535542-9
	93.98[3.700]	96.52[3.800]	76	3-535542-8
	91.44[3.600]	93.98[3.700]	74	3-535542-7
	88.90[3.500]	91.44[3.600]	72	3-535542-6
	86.36[3.400]	88.90[3.500]	70	3-535542-5
	83.82[3.300]	86.36[3.400]	68	3-535542-4
	81.28[3.200]	83.82[3.300]	66	3-535542-3
	78.74[3.100]	81.28[3.200]	64	3-535542-2
	76.20[3.000]	78.74[3.100]	62	3-535542-1
	73.66[2.900]	76.20[3.000]	60	3-535542-0
	71.12[2.800]	73.66[2.900]	58	2-535542-9
	68.58[2.700]	71.12[2.800]	56	2-535542-8
	66.04[2.600]	68.58[2.700]	54	2-535542-7
	63.50[2.500]	66.04[2.600]	52	2-535542-6
	60.96[2.400]	63.50[2.500]	50	2-535542-5
	58.42[2.300]	60.96[2.400]	48	2-535542-4
	55.88[2.200]	58.42[2.300]	46	2-535542-3
	53.34[2.100]	55.88[2.200]	44	2-535542-2
	50.80[2.000]	53.34[2.100]	42	2-535542-1
	48.26[1.900]	50.80[2.000]	40	2-535542-0
	45.72[1.800]	48.26[1.900]	38	1-535542-9
	43.18[1.700]	45.72[1.800]	36	1-535542-8
	40.64[1.600]	43.18[1.700]	34	1-535542-7
	38.10[1.500]	40.64[1.600]	32	1-535542-6
	35.56[1.400]	38.10[1.500]	30	1-535542-5
	33.02[1.300]	35.56[1.400]	28	1-535542-4
	30.48[1.200]	33.02[1.300]	26	1-535542-3
	27.94[1.100]	30.48[1.200]	24	1-535542-2
	25.40[1.000]	27.94[1.100]	22	1-535542-1
	22.86[.900]	25.40[1.000]	20	1-535542-0
	20.32[.800]	22.86[.900]	18	535542-9
	17.78[.700]	20.32[.800]	16	535542-8
	15.24[.600]	17.78[.700]	14	535542-7
	12.70[.500]	15.24[.600]	12	535542-6
		10.16[.400]	10	535542-5
		7.62[.300]	8	535542-4
		5.08[.200]	6	535542-3
		2.54[.100]	4	535542-2
		-	2	535542-1
FINISH	B	A	NO OF POSN	PART NUMBER

535542

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 06NOV2002		 TE Connectivity Ltd.			
		CHK J.OLSON 06NOV02					
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU			
		APVD J.OLSON 06NOV02					
		PRODUCT SPEC 108-25022					
		APPLICATION SPEC 114-25018					
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				WEIGHT -	A2 00779	C=535542	-
CUSTOMER DRAWING					SCALE	SHEET	REV
					1:1	2 of 2	V

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-535542-5](#)