

PART NUMBER	REV	FIRST USED
567907-1	D	854040-3


TERMINAL NAME:		CRIMPING DATA			
PIN CONTACT, SPECIAL		VISIBLE PAD LTR	CRIMP HEIGHT	WIRE SIZE	
	787113	A	NOT	USED	
		B	NOT	USED	
		C	.025 ±.001	24	
		D	.023 ±.001	26-28	
CRIMP	SIZE	TYPE	RANGE		
WIRE	.042	F	28-24		
INSUL	.042	0	.020-.025		
FEED	APPL INST	SET UP GAGE	LAYOUT		
.300	SEE CUSTOMER MANUAL	NONE	L1585		
TERM APPL SPEC	-	WIRE STRIP LENGTH	-		

SIM TO HDM 680106

QTY	REV	DESCRIPTION	PART NO	ITEM NO	
				70	
				69	
				68	
				67	
				66	
				65	
				64	
				63	
				62	
				61	
				60	
				59	
				58	
				57	
REF	-	B	694433-8	PAWL, FEED	56
					55
					54
					53
					52
1	-	A	811242-2	BUMPER, HOLDDOWN	51
1	-	A	690753-1	SPACER, TONKER	50
					49
1	-	A	690602-6	CAM, PRE-FEED 1.62 STROKE	48
					47
					46
1	-	A	690191-1	PLUG, NYLON	45
1	-	C	455673-1	RAM	44
1	-	A	690125-1	WASHER, LAMINATED	43
1	-	A	690124-1	WASHER, RAM	42
1	-	A	7-21002-9	BOLT, CRIMPER (5/16x1.00)	41
1	-	A	23241-6	BALL, STEEL	40
1	-	A	690170-1	SPRING, COMPRESSION	39
1	-	C	690142-1	DISC, INSULATION	38
1	-	D	354777-1	WIRE DISC, PLASTIC	37
1	-	A	22480-5	WASHER, SPRING	36
1	-	B	690212-1	POST, RAM	35
1	-	B	2-690786-3	SUPPORT, TERMINAL	34
1	-	C	462544-1	PLATE, BASE SPECIAL	33
1	-	A	690432-3	SCREW, ADJUSTMENT	32
1	-	B	462543-1	BLOCK, SCREW SPECIAL	31
1	-	B	455689-1	BLOCK, STRIP GUIDE ADJ	30
1	-	C	843869-1	PLATE, STRIP GUIDE	29
1	-	C	1-455888-4	SPACER, FRONT SHEAR DEP	28
2	-	A	1-22284-0	SPRING, DRAG	27
1	-	B	240793-1	LEVER, DRAG RELEASE	26
1	-	B	240792-1	DRAG, TERMINAL	25
1	-	D	6-690504-4	GUIDE, STRIP (REAR)	24
1	-	A	690438-1	GUIDE, STRIP (FRONT)	23
					22
1	-	A	463756-1	GUIDE, SCRAP	21
					20
REF	-	C	462615-1	STRIPPER	19
					18
					17
					16
					15
					14
					13
1	-	A	5-22280-0	SPRING, SHEAR	12
1	-	B	690461-2	STOP, SHEAR (FRONT)	11
1	-	B	462548-1	HOLDER, SHEAR (FRONT) SP	10
1	-	B	462547-1	SHEAR, FLOAT (FRONT) SP	9
1	-	C	6-683403-9	ANVIL	8
					7
					6
1	-	A	462838-1	DEPRESSOR, SHEAR (FRONT) SP	5
1	-	B	238011-7	SPACER, BLOCK CRIMPER	4
1	-	C	6-683454-9	CRIMPER, INSULATION	3
1	-	C	455888-6	SPACER, CRIMPER	2
1	-	C	2-456401-1	CRIMPER, WIRE	1

THIS DRAWING IS A CONTROLLED DOCUMENT.

THIS DRAWING IS UNCLASSIFIED - RELEASED FOR PUBLICATION 2014/03/02 BY AMP INCORPORATED. ALL RIGHTS RESERVED.



- 1 RECOMMENDED SPARE PARTS.
- 2 GREASE LIGHTLY.
- 3 ITEM NOT SHOWN
- 4 CUT TO LENGTH AT ASSEMBLY.

QTY	REV	DESCRIPTION	PART NO	ITEM NO	
				129	
				128	
2	-	C	7-354779-6	PIN, WIRE DISC (.3370)B	127
2	-	C	7-354779-2	PIN, WIRE DISC (.3350)A	126
1	-	A	986950-1	WASHER, FLAT PRECISION	125
				124	
1	-	B	690701-2	PLATE, SERIAL NO.	123
				122	
1	-	A	4-21028-0	PIN, SLT SPR (Ø.093x.75) ST GDE PL	121
				120	
2	-	A	21899-2	WASHER, FLAT (#10) S G ADJ BLK	119
				118	
2	-	A	21024-5	WASHER, LOCK (#10) ADJ BLOCK	117
				116	
				115	
2	-	A	21024-2	WASHER, LOCK (#4) FRONT STP GUIDE	114
REF	-	A	21024-4	WASHER, LOCK (#8) FEED FINGER	113
2	-	A	21024-4	WASHER, LOCK (#8) DEP-HOLD	112
REF	-	A	21024-4	WASHER, LOCK (#8) STRIPPER	111
				110	
				109	
1	-	A	21018-5	NUT, HEX (#6) HOLD DOWN	108
				107	
				106	
1	-	A	22353-8	SCR, SHLD (Ø.187x.25) DRAG LEVER	105
				104	
1	-	A	21009-2	SCR, SKT 5ET (1/4-20x.25 LW) RAM	103
				102	
4	-	A	21017-2	SCR, DRIVE (#2x.19) ID PLATE	101
1	-	B	819347-1	PLATE, IDENTIFICATION	100
2	-	A	3-21002-0	SCR, BHC (10-32x.88) DRAG	99
1	-	A	22733-8	SCR, BHC (8-32x.38 LW) ANVIL	98
				97	
1	-	A	3-21000-8	SCR, SHC (10-32x.88) MOUNTING	96
1	-	A	2-21002-7	SCR, BHC (10-32x.50) S6 ADJ BLK	95
4	-	A	2-21002-2	SCR, BHC (8-32x.50) SHEAR-TERM SUP	94
2	-	A	2-21002-1	SCR, BHC (8-32x.38) R STP GDE	93
				92	
1	-	A	1-21002-7	SCR, SHC (6-32x.50) CAM	91
2	-	A	2-21000-7	SCR, SHC (8-32x.50) SCR BLK	90
				89	
				88	
2	-	A	2-21000-7	SCR, SHC (8-32x.48) DEP-HOLD DOWN	87
REF	-	A	2-22603-0	SCR, HEX HD (8-32x.31) FEED FINGER	86
2	-	A	1-21000-3	SCR, SHC (4-40x.25) F ST GUIDE	85
REF	-	A	22733-9	SCR, BHC (8-32x.50 SL) STRIPPER	84
				83	
				82	
1	-	A	3-22603-1	SCR, HEX (10-32x.38) S6 ADJ BL	81
				80	
				79	
				78	
2	-	B	463310-8	BLADE, STRIPPING (#26)	77
				76	
				75	
1	-	A	690603-1	SPRING, ASSIST	74
1	-	A	23030-1	SCR, SKT CAP (6-32x.25) CP DSC	73
				72	
				71	

QTY	REV	DESCRIPTION	PART NO	ITEM NO
-1	U/M	DWG SIZE		

QTY	REV	DESCRIPTION	PART NO	ITEM NO
-1	U/M	DWG SIZE		

REV	DATE	DESCRIPTION
1	7/13/94	RELEASED

REV	DATE	DESCRIPTION
1	7/13/94	RELEASED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[567907-1](#)