


LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			BI	REVISED PER ECO-11-005931	23MAR2011	HMR	CR



1

MATERIALS AND FINISH:
HOUSING: PA 6-6, UL 94-V0, COLOR: SEE P/N TABLE.
CLAMP: BRASS, NICKEL PLATED.
DOUBLE SIDE CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2

WIRE SIZE RANGE
SOLID WIRE: 12-30AWG
STRANDED WIRE: 12-30AWG

3

RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE N° E60677.

4

IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.

5

NOT CUMULATIVE TOLERANCE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.2

1 PLC ±0.2

2 PLC ±0.2

3 PLC ±0.001

4 PLC ±0.0001

ANGLES ±2

FINISH

1

-

DWN 28MAR2001 E. ZANOLINI

CHK 28MAR2001 D. BIEVENOUR

APVD 28MAR2001 D. BIEVENOUR

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL BLOCK, PLUG
7.62mm PITCH

SIZE A2

CAGE CODE 00779

DRAWING NO C-796981

RESTRICTED TO -

SCALE NTS

SHEET 1 OF 1

REV BI

GREEN	89.44	12	1-796981-2
GREEN	81.82	11	1-796981-1
GREEN	74.20	10	1-796981-0
GREEN	66.58	9	796981-9
GREEN	58.96	8	796981-8
GREEN	51.34	7	796981-7
GREEN	43.72	6	796981-6
BLACK	36.10	5	2-796981-5
GREEN	36.10	5	796981-5
GREEN	28.48	4	796981-4
GREEN	20.86	3	796981-3
GREEN	13.24	2	796981-2
COLOR	DIM L.	NO OF POSN	PART NUMBER

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[796981-4](#)