





LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			BI	REVISED PER ECO-11-005931	23MAR2011	HMR	CR

D

C

B

A



796981-3 AS SHOWN

- 1

MATERIALS AND FINISH:
HOUSING: PA 6-6, UL 94-V0, COLOR: SEE P/N TABLE.
CLAMP: BRASS, NICKEL PLATED.
DOUBLE SIDE CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
- 2




WIRE SIZE RANGE
SOLID WIRE: 12-30AWG
STRANDED WIRE: 12-30AWG
- 3

RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE N° E60677.
- 4

IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.
- 5

NOT CUMULATIVE TOLERANCE

GREEN	89.44	12	1-796981-2
GREEN	81.82	11	1-796981-1
GREEN	74.20	10	1-796981-0
GREEN	66.58	9	796981-9
GREEN	58.96	8	796981-8
GREEN	51.34	7	796981-7
GREEN	43.72	6	796981-6
BLACK	36.10	5	2-796981-5
GREEN	36.10	5	796981-5
GREEN	28.48	4	796981-4
GREEN	20.86	3	796981-3
GREEN	13.24	2	796981-2
COLOR	DIM L.	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 28MAR2001		<div><div>TE Connectivity</div><div>NAME</div><div>TERMINAL BLOCK, PLUG 7.62mm PITCH</div><div>-</div><div>SIZE</div><div>CAGE CODE</div><div>DRAWING NO</div><div>RESTRICTED TO</div></div>							
DIMENSIONS: mm		CHK D. BIEVENOUR 28MAR2001									
		APVD D. BIEVENOUR 28MAR2001									
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.001 4 PLC ±0.0001 ANGLES ±2 FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -									
MATERIAL 	-	CUSTOMER DRAWING		A200779		C-796981					
				SCALE	NTS	SHEET	1	OF	1	REV	BI

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[796981-6](#)