

4

© Copyright 2020 BY TE Connectivity

3

2

1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	06.02.2020	SI	SI

LKZ16 - Variant Overview

SYMBOL	PN/DESC	MATERIAL AND COLOR
	241640-000 LKZ16 L1	MATERIAL: PV501, Soft-PVC white matt (0,08 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 1-color hot-stamping black, PRP 912
	469096-000 LKZ16 L2	MATERIAL: PV501, Soft-PVC white matt (0,08 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 1-color hot-stamping black, PRP 912
	471872-000 LKZ16 L3	MATERIAL: PV501, Soft-PVC white matt (0,08 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 1-color hot-stamping black, PRP 912
	8-1768034-4 LKZ16 L-PLUS	MATERIAL: PV501, Soft-PVC white matt (0,08 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 1-color hot-stamping black, PRP 912
	8-1768034-3 LKZ16 L-MINUS	MATERIAL: PV501, Soft-PVC white matt (0,08 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 1-color hot-stamping black, PRP 912
	8-1768034-2 LKZ16 E	MATERIAL: PV501, Soft-PVC white matt (0,08 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 1-color hot-stamping black, PRP 912
	571868-000 LKZ16 N	MATERIAL: PV501, Soft-PVC white matt (0,08 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 1-color hot-stamping blue, PRV 925
	708798-000 LKZ16 PE	MATERIAL: PV003, Soft-PVC „warning-yellow“ gloss (0,07 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 2-color hot-stamping back and green, PRP 912 and PRP 975
	8-1768034-5 LKZ16 PEN	MATERIAL: PV003, Soft-PVC „warning-yellow“ gloss (0,07 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 2-color hot-stamping back and green, PRP 912 and PRP 975
	7-1768034-8 LKZ16 B4	MATERIAL: PV003, Soft-PVC „warning-yellow“ gloss (0,07 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 2-color hot-stamping back and green, PRP 912 and PRP 975
	7-1768034-5 LKZ16 B1	MATERIAL: PV501, Soft-PVC white matt (0,08 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 1-color hot-stamping black, PRP 912
	7-1768034-6 LKZ16 B2	MATERIAL: PV501, Soft-PVC white matt (0,08 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 1-color hot-stamping black, PRP 912

SYMBOL	PN/DESC	MATERIAL AND COLOR
	7-1768034-7 LKZ16 B3	MATERIAL: PV501, Soft-PVC white matt (0,08 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 1-color hot-stamping black, PRP 912
	7-1768034-9 LKZ16 B5	MATERIAL: PV501, Soft-PVC white matt (0,08 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 1-color hot-stamping black, PRP 912
	8-1768034-0 LKZ16 B6	MATERIAL: PV501, Soft-PVC white matt (0,08 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 1-color hot-stamping black, PRP 912
	8-1768034-1 LKZ16 B7	MATERIAL: PV501, Soft-PVC white matt (0,08 mm) LAMINATE: PE103, Polyester clear gloss (0,023 mm) PRINT: 1-color hot-stamping black, PRP 912

Presentation

Quantity per sheet: 10 PCs

Labels across: 2 x 5

TE PN: see variant table

LABEL BUILD DETAILS	TOLERANCES mm [INCH]	THIS DRAWING IS A CONTROLLED DOCUMENT
LAMINATE	LABEL HEIGHT: ±0,3 [.012]	DIMENSIONS mm [INCHES] TOLERANCES UNLESS OTHERWISE SPECIFIED 0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH GLOSS UNPRINTED MATT PRINTED
PRINT	LABEL WIDTH: ±0,3 [.012]	
MATERIAL	WEB WIDTH: ±0,8 [.031]	
ADHESIVE	VERTICAL REPEAT: ±0,8 [.031]*	
LINER	HORIZONTAL REPEAT: ±0,8 [.031]*	
	PRINT POSITIONING: ±0,8 [.031]*	
	LEFT MARGIN: ±0,4 [.016]	
	QUANTITY: -0% +2%	
	*NON ACCUMULATING	

PRINT	see variant table
MATERIAL	see variant table
ADHESIVE TYP	see variant table
LINER	KRAFT Liner, siliconised
DWN S. Iser / 06.02.2020	DATE
CHK S. Iser / 06.02.2020	DATE
APVD S. Iser / 06.02.2020	DATE
PRODUCT SPEC	DATE
APPLICATION SPEC	DATE
WEIGHT 0,01 g	
CUSTOMER DRAWING	

Size: A2

CAGE CODE: C2290

DRAWING NO: C-LKZ16

RESTRICTED TO:

SHEET 1 of 1

REV A1

All dimensions in mm [inch]

labels are centered on the liner as long as not declared separately

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[708798-000](#) [6-1768048-6](#)