


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	09SEP2021	GK	DB

LABEL AND LINER DESIGN




All dimensions in mm [Inches]

TE PN: F28486-000

**OUTSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 2500**


PRESENTATION




MATERIAL	POLYVINYL FLUORIDE (TEDLAR®)
ADHESIVE TYPE	PERMANENT ACRYLIC
LINER	BROWN KRAFT

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

<p>DIMENSIONS:</p> <p>mm [INCHES]</p>	<p>TOLERANCES UNLESS OTHERWISE SPECIFIED:</p>												
	<table border="0"> <tr> <td>0 PLC</td><td>± .</td></tr> <tr> <td>1 PLC</td><td>± .</td></tr> <tr> <td>2 PLC</td><td>± .</td></tr> <tr> <td>3 PLC</td><td>± .</td></tr> <tr> <td>4 PLC</td><td>± .</td></tr> <tr> <td>ANGLES</td><td>± .</td></tr> </table>	0 PLC	± .	1 PLC	± .	2 PLC	± .	3 PLC	± .	4 PLC	± .	ANGLES	± .
0 PLC	± .												
1 PLC	± .												
2 PLC	± .												
3 PLC	± .												
4 PLC	± .												
ANGLES	± .												
<p>MATERIAL</p> <p>SEE TABLE</p>	<p>FINISH</p> <p>—</p>												

DWN	09SEP2021	 TE Connectivity			
GOPALAKRISHNA HV					
CHK	09SEP2021	NAME TEDLAR® LABEL – WHITE – 1 ACROSS 76.2mm x 50.8mm (3.0inch x 2.0inch) —			
D.BURGAT					
APVD	09SEP2021				
D.BURGAT					
PRODUCT SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED T			
TTDS-138					
APPLICATION SPEC					
—		A3 FB1U7 C-PVF-762508-2.5-9 —			
WEIGHT					
0.530g					
CUSTOMER DRAWING		SCALE	SHEET	REV	
		NTS	1 OF 1	A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[F28486-000](#)