


794141-3 Product Details

 Product View

794141-3

 Part Status is Active

[Active](#)

4.2mm (.165") Centerline, 600 V, 9 A max. Dual Action
[Not EU RoHS or ELV Compliant \(Find RoHS Compliant Alternates\)](#)

Product Highlights:

- Contact
- AMP-DUAC
- Socket
- Wire Range = 0.30-0.90² [22-18] mm [AWG]
- Gold (30) Contact Mating Area Plating

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [CONTACT, SOCKET, AMP-DUAC\(TM\) POWER CONNECTOR LOOSE...](#) (PDF, English)

Catalog Pages/Data Sheets:

- [AMP-DUAC CONNECTORS](#) (PDF, English)
- [INTERCONNECTS FOR NETWORKING](#) (PDF, English)
- [MULTI-USER SYSTEMS](#) (PDF, English)
- [SOFT SHELL PIN AND SOCKET CONNECTORS](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- [AMP-DUAC Headers and Connectors](#) (PDF, English)
- [AMP-DUAC/PL \(Position Lock\) Connectors](#) (PDF, English)
- [AMP-DUAC/PL* \(Position Lock\) Connectors](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Contact
- [Connector Line](#) = AMP-DUAC
- [Gender](#) = Socket
- [Insulation Diameter \(mm \[in\]\)](#) = 1.50-2.40 [.059-.094]

Termination Related Features:

- Solder Tail Contact Plating = Tin-Lead

Body Related Features:

- [Wire Range \(mm \[AWG\]\)](#) = 0.30-0.90² [22-18]

Languages: English | [Deutsch](#) | [Español](#) | [Português \(do Brasil\)](#) | [Русский](#) | [Italiano](#) | [\(\)](#) | [\(\)](#) | [\(\)](#)

Country Sites: [China](#) | [Japan](#)

[Provide Website Feedback](#) | [Contact Customer Support](#)

[Home](#) | [Customer Support](#) | [Supplier](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)

© 2007 Tyco Electronics Corporation All Rights Reserved

Contact Related Features:

- [Contact Mating Area Plating](#) = Gold (30)
- Contact Material = Phosphor Bronze

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Packaging Related Features:

- [Packaging Method](#) = Loose Piece

Other:

- Brand = AMP

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[794141-3](#)