



7-2232359-5 Product Details



7-2232359-5

TE Internal Number: 7-2232359-5



Power Triple Lock Connector System

Not reviewed for RoHS Compliance

Product Highlights:

- Power Triple Lock Product Line
- Wire-to-Wire
- Applies To Wire/Cable
- Connector
- Connector Assembly

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Documentation & Additional Information	
Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.	Related Products: <ul style="list-style-type: none"> • Tooling

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Line = Power Triple Lock • Product Type = Connector • Connector Type = Connector Assembly <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> • Panel Mount Retention = Without • Mount = Free Hanging • Mating Retention Type = Latching <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Operating Voltage (VAC) = 600 • Operating Voltage (VDC) = 600 <p>Body Features:</p> <ul style="list-style-type: none"> • Mating Retention = With • Row-to-Row Spacing (mm [in]) = 8.10 [0.319] <p>Contact Features:</p> <ul style="list-style-type: none"> • Contact Layout = Double Row <p>Housing Features:</p> <ul style="list-style-type: none"> • Connector Style = Receptacle • Centerline (mm [in]) = 6.00 [0.236] • Housing Material = Nylon - GF • Housing Color = Green 	<p>Configuration Features:</p> <ul style="list-style-type: none"> • Number of Positions = 10 <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = Not reviewed for ELV/RoHS compliance • UL Flammability Rating = UL 94V-0 • Agency/Standard = IEC60335-1 750C NF <p>Identification Marking:</p> <ul style="list-style-type: none"> • Keying = C <p>Environmental:</p> <ul style="list-style-type: none"> • Operating Temperature (°C [°F]) = -55 - +105 [-67 - +221] • Halogen Free = No <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • Applies To = Wire/Cable • Glow Wire Rating = Glow Wire <p>Operation/Application:</p> <ul style="list-style-type: none"> • Application Use = Wire-to-Wire • Contact Transmits (Typical Application) = Power <p>Other:</p> <ul style="list-style-type: none"> • Brand = TE Connectivity

Feedback

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [AODA Accessibility Policy](#)
- [AODA Multi-Year Accessibility Plan](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-2232359-5](#)