



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
031	REVISED	DAC 6/15/99	<i>DCam</i> 6/16/99

HOUSING COUPLING NUT CAP	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	PASSIVATE PER ASTM-A380
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BRASS PER ASTM-B-16 HALF HARD	GOLD PLATE PER MIL-G-45204
RETAINING RING	BERYLLIUM COPPER PER ASTM-B-194, ALLOY C17200, COND H	N/A
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A
FERRULE	COPPER OR BRASS ALLOY ROCKWELL F65 MAXIMUM	GOLD PLATE PER MIL-G-45204
COMPONENT	MATERIAL	FINISH

NOTES:

- DESIGNED FOR USE WITH
RG174 AND RG316 CABLE
- CAPTURED CENTER CONTACT

CABLE ENTRY DIAMETER MINIMUM	
HOUSING ADAPTER	.062
OUTER SLEEVE	.125

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCE ON
FRAC. DEC. ANGLES
± 1/64 ± .005 ± °

These drawings and specifications are the property of AMP Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.

DRAWN BY
E.F. HOYLE DATE
1/24/89
CHECKED BY
L. ROSS DATE
2/10/89
APPD BY
[Signature] DATE
2/22/89

USE ASS'Y PROCEDURE

408-04846
NO. AP. (20-584)



AMP Incorporated
140 Fourth Avenue
Waltham, MA 02451-7599

TITLE OSM RIGHT ANGLE CABLE PLUG
CRIMP ATTACHMENT
M39012/56-3026 CAT C

SIZE B	CODE IDENT NO. 26805	2037-8026-92	REV 03 ₁
SCALE 5:1		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M39012/56-3026](#)