


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19 .  
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
A	4	P	LTR	DESCRIPTION	DATE	DWN	APVD
			M4	ECR-06-002958	2-06	MY	TE
			M5	ECR-06-003076	2-06	MY	GB

PART NUMBER	REV	FIRST USED
671505	M	1-471273-3

APPLICATOR PARTS LIST				TYPE					
				LENGTHWISE	I.D. BAND				
NO.	DESCRIPTION	REQ.	PART NO.	NO.	DESCRIPTION	REQ.	PART NO.	CRIMPING DATA	TERMINALS
1	△ WIRE CRIMPER			42	COMP SPRING (TABLE)	2	803036-1	TO APPLY TERMINAL NONE	40681
2	△ INS CRIMPER, .262 THK	1	375679	43	COVER PLATE	2	375680		40942
3	△ ANVIL	1	375687	44	FEED BLOCK LEFT	1	376659	WIRE SIZE	CRIMP HEIGHT
4	ANVIL, INDENTER	1	375684	45	FEED BLOCK RIGHT	1	376658	△ 2	△ 3
5	△ SHEAR BLADE	1	375683	46	FEED LINK	1	376656		
6	△ REAR SHEAR PLATE			47	FEED PIN (FEED BLOCK)	1	376657		
7	SHEAR BLADE SPACER			48					
8	△ FRONT SHEAR PLATE			49	TO BE USED ONLY WHEN INDENTING IS REQUIRED				
9	REAR ANVIL SPACER PL			50					
10	FRONT ANVIL SPACER PL			51	INDENTOR HOLDER	1	375676	CRIMP	SIZE
11	TOOL SPACER			52	INDENTOR HOLDER KEY	1	376075	WIRE	TYPE
12	CRIMP SPACER			53	INDENTOR HOLDER PIN	1	375675	INSUL.	FEED
13	STRIP GUIDE	1	376662	54	INDENTORS	-	374595	SLEEVED	
14	STOCK DRAG	1	376663	55	-	-	-	INSULATION RANGE	WIRE RANGE
				56	INDENTOR SPACER	-	378389	.125 - .220	
15	RAM	1	471167	57				EXPLODED VIEW	MEXICO FEED
16	TOOL HOLDER	1	471662	58				A-6012-1 A-6012-2	.325*
17	ADJ. CRIMP MOUNT			59				REMARKS:	155365
18	ADJ. BLOCK			60				ONE TERMINAL AT A TIME	
19	APPLICATOR MOUNT ASSY.			61				1, 2 OR 3 DIGITS AS REQUIRED	
20	BASE PLATE	1	471658	62					
21	BASE BLOCK	1	471659	63	SCR, DRIVE #4 X .25	3	21017-6		
22	STRIP GUIDE PL FLOATING	1	471660	64	PLATE, IDENTIFICATION	1	452373-1		
23	ANVIL HOLDER	-	-	65	-	1	-		
24	AUX. ANVIL HOLDER	-	-	MISCELLANEOUS					
25	STRIPPER	1	375690	66	-	-	-		
26	STRIPPER MOUNT	1	377811	67	-	-	-		
27	RETAINING PLATE	-	-	68	-	-	-		
28	STRIPPER MOUNT BRACKET			69	-	-	-		
29	STRIPPER BUSHING			70					
30	STOCK DRAG CONTROL BRKT	1	465870-1	71	-	-	-		
31	STOCK DRAG HANDLE	-	-	72	-	-	-		
32	STOCK DRAG STUD	-	-						
33	STOCK DRAG SPRING	2	3-22284-9						
34	STOCK DRAG ADJ. SCREW	2	372997						
35	FEED FINGER HOLDER								
36	FEED FINGER	1	376655-1						
37	FEED FINGER SPRING	1	376661-1						
38	FEED FINGER PIN	1	21030-7						
39	BASE CASTING	1	570238						
40	GUARD	1	459401-1						
41	TABLE MOUNTS	2	375689						

- △ 1 RECOMMENDED SPARE PARTS.
- △ 2 INSULATION RANGE .125-.220
- △ 3 CRIMP TILL TIGHT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. YOUNGER 28MAR03	<b>AMP</b> Tyco Electronics Harrisburg, PA 17105-3608
DIMENSIONS: IN		CHK T. ELBIN 31MAR03	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T. ELBIN 31MAR03	
		PRODUCT SPEC -	NAME
MATERIAL		APPLICATION SPEC -	END FEED STD APPLICATOR
FINISH		WEIGHT -	SIZE A3
		CUSTOMER DRAWING	CAGE CODE 00779
			DRAWING NO C-671505
			SCALE 1:1
			SHEET 1 OF 1
			REV M5

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[671505](#)