








THIS DRAWING IS A CONTROLLED DOCUMENT.



 DO NOT REVISE EXCEPT BY CAD	LOC	DIST	REVISIONS					
	AP	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C1		REVISED DRAWING ECO-13-004694	02APR13	NCL	MG



CORTE B-B SECTION B-B

CORTE C-C SECTION C-C

WIRE RANGE 1,0-1,5mm ² ISUL. RANGE DIA. 1,4-2,4	PRÉ-PRATEADO PRÉ-SILVER	LATÃO BRASS	880698-3
	PRÉ-ESTANHADO PRE TIN	BRONZE FOSFOROSO PHOS. BRONZE	880698-2
	PRÉ-ESTANHADO PRE TIN	LATÃO BRASS	880698-1
	FINISH	MATERIAL	PART NUMBER

DIMENSIONS: mm		DWN	25JAN01	MATERIAL	VER TABELA/SEE TABLE	FINISH	VER TABELA/SEE TABLE
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	25JAN01	 TE Connectivity			
0 PLC ± -		APVD	25JAN01				
1 PLC ± 0.3		PRODUCT SPEC		NAME			
2 PLC ± -		APPLICATION SPEC		TERMINAL, 1.8 ECONOSEAL "J" SERIES MARK II+ REC.			
3 PLC ± 3		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
4 PLC ± -		CUSTOMER DRAWING		A4	00779	©=880698	—
ANGLES ±		SCALE		SHEET		REV	
		1:1		1 of 1		C1	

THIS DRAWING IS UNPUBLISHED. ALL RIGHTS RESERVED.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[880698-2](#)