

4

3

2

1

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

2015

© COPYRIGHT 2001

BY TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED PER PCN E-17-004158	22MAR2017	JA	DM
	G	REVISED PER ECR-20-016547	19NOV2020	EC	IG
	G1	REVISED PER PCN-22-157685	02NOV2022	CO	IG
	G2	REVISED PER PCN-23-194869	11DEC2023	CO	CB

8-32 X 1 1/8 2A-RH
SLOTTED FILLISTER HEAD STAINLESS STEEL SCREW
WITH STAINLESS STEEL LOCK WASHER (2 REQ'D)
MAX TORQUE 17 IN-LB [1.92 N-M]

C (MAX O.D. CABLE DIA.
ON SIZE 24 ONLY FOR
BIGGER BUSHING)

XX SIZE	TE INTERNAL PART NO.	DEUTSCH PART NO.	BUSHINGS SIZE (NEOPRENE) 2	CLAMP THREAD CLASS 2B	A ±.050 [1.27]	B ±.025 [.635]	C ±.050 [1.27]	D MAX.
18	0409-201-1800	0409-201-1800	18	1.188-18 UNEF	.938 [23.82]	1.469 [37.31]	.625 [15.87]	1.800 [45.72]
24	0409-201-2400	0409-201-2400	18 AND 24	1.438-18 UNEF	1.031 [26.19]	1.688 [42.88]	.750 [19.05]	1.700 [43.18]

4. BUSHING NO UV CERTIFICATE, UV EXPOSURE NOT RECOMMENDED.

3. THE OPERATING TEMPERATURE IS -55°C TO 125°C.

2 BUSHINGS ARE SHIPPED LOOSE WITH CABLE CLAMP ASSEMBLIES IN A SEALED PLASTIC BAG. PART NUMBER LABEL AND COUNTRY OF ORIGIN, IF OTHER THAN USA, ON THE BAG.

1. FINISH: TIN OVER NICKEL PLATE. MAY DISCOLOR.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 02MAR2001

ALEX ROLINSKI

CHK 08JUN2004

JAIME C. APOSTOL

APVD 14JUN2004

ROBIN REED

PRODUCT SPEC

N/A

APPLICATION SPEC

N/A

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

CABLE CLAMP
HD30 SERIES

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 4AFU8 C=0409-201-XX00 -

SCALE 2:1 SHEET 1 OF 1 REV G2

DIMENSIONS:

INCHES [mm]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±.025 [0.64]

4 PLC ±

ANGLES ±0°30'0"

FINISH N/A

1470-19 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[0409-201-2400](#)