






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	26AUG2020	CL	IG

TE INTERNAL PN	DEUTSCH PN	PLATING
0462-006-1631	0462-006-1631	GOLD

1. SEE APPLICATION SPECIFICATION FOR CRIMP TOOLS AND WIRE RANGE.
FOR HAND CRIMP:
22AWG [0.35] USE HDT-48-00 HAND CRIMPING TOOL.
24AWG [0.22] USE M22520/7-1 HAND CRIMPING TOOL WITH M22520/7-3 POSITIONAL.NGE.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. LIEW 26AUG2020		<div></div> <div>TE Connectivity</div>			
DIMENSIONS: INCHES [mm]	<div><div></div></div>	CHK D. MEYER 26AUG2020					
		APVD I. GRANICHAROVA 26AUG2020					
		PRODUCT SPEC 108-151004					
<div></div>	<div>0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±</div>	APPLICATION SPEC 114-151004		NAME CONTACT SOCKET SIZE 16			
		WEIGHT 0.60g		SIZE A3	CAGE CODE 4AFU8	DRAWING NO C-0462-006-16XX	RESTRICTED TO -
		CUSTOMER DRAWING		SCALE 10:1	SHEET 1 OF 1	REV A	
MATERIAL COPPER ALLOY		FINISH SEE TABLE					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[0462-006-1631](#)