

8

7

6

5

4

3

2

1

TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-

<div>8</div> <div>8</div>	<div>9</div>	<div>7</div>	41.15 [1.620]	43.05 [1.695]	15	16	2-103673-6	
		<div>7</div>	18.29 [.720]	20.19 [.795]	6	7	2-103673-5	
		<div>1</div>	64.01 [2.520]	65.91 [2.595]	24	25	2-103673-4	
		<div>1</div>	61.47 [2.420]	63.37 [2.495]	23	24	2-103673-3	
		<div>1</div>	58.93 [2.320]	60.83 [2.395]	22	23	2-103673-2	OBSOLETE
		<div>1</div>	56.39 [2.220]	58.29 [2.295]	21	22	2-103673-1	
		<div>1</div>	53.85 [2.120]	55.75 [2.195]	20	21	2-103673-0	OBSOLETE
		<div>1</div>	51.31 [2.020]	53.21 [2.095]	19	20	1-103673-9	
		<div>1</div>	48.77 [1.920]	50.67 [1.995]	18	19	1-103673-8	OBSOLETE
		<div>1</div>	46.23 [1.820]	48.13 [1.895]	17	18	1-103673-7	
		<div>1</div>	43.69 [1.720]	45.59 [1.795]	16	17	1-103673-6	
		<div>1</div>	41.15 [1.620]	43.05 [1.695]	15	16	1-103673-5	
		<div>1</div>	38.61 [1.520]	40.51 [1.595]	14	15	1-103673-4	
		<div>1</div>	36.07 [1.420]	37.97 [1.495]	13	14	1-103673-3	
		<div>1</div>	33.53 [1.320]	35.43 [1.395]	12	13	1-103673-2	OBSOLETE
		<div>1</div>	30.99 [1.220]	32.89 [1.295]	11	12	1-103673-1	
		<div>1</div>	28.45 [1.120]	30.35 [1.195]	10	11	1-103673-0	
		<div>1</div>	25.91 [1.020]	27.81 [1.095]	9	10	103673-9	
		<div>1</div>	23.37 [.920]	25.27 [0.995]	8	9	103673-8	
		<div>1</div>	20.83 [.820]	22.73 [.895]	7	8	103673-7	
<div>1</div>	18.29 [.720]	20.19 [.795]	6	7	103673-6			
<div>1</div>	15.75 [.620]	17.65 [.695]	5	6	103673-5			
<div>1</div>	13.21 [.520]	15.11 [.595]	4	5	103673-4			
<div>1</div>	10.67 [.420]	12.57 [.495]	3	4	103673-3			
<div>1</div>	8.13 [.320]	10.03 [.395]	2	3	103673-2			
<div>1</div>	5.59 [.220]	7.49 [.295]	1	2	103673-1			
REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.		

<div>8</div> <div>8</div>	<div>9</div>	<div>7</div>	41.15 [1.620]	43.05 [1.695]	15	16	2-103673-6	
		<div>7</div>	18.29 [.720]	20.19 [.795]	6	7	2-103673-5	
		<div>1</div>	64.01 [2.520]	65.91 [2.595]	24	25	2-103673-4	
		<div>1</div>	61.47 [2.420]	63.37 [2.495]	23	24	2-103673-3	
		<div>1</div>	58.93 [2.320]	60.83 [2.395]	22	23	2-103673-2	OBSOLETE
		<div>1</div>	56.39 [2.220]	58.29 [2.295]	21	22	2-103673-1	
		<div>1</div>	53.85 [2.120]	55.75 [2.195]	20	21	2-103673-0	OBSOLETE
		<div>1</div>	51.31 [2.020]	53.21 [2.095]	19	20	1-103673-9	
		<div>1</div>	48.77 [1.920]	50.67 [1.995]	18	19	1-103673-8	OBSOLETE
		<div>1</div>	46.23 [1.820]	48.13 [1.895]	17	18	1-103673-7	
		<div>1</div>	43.69 [1.720]	45.59 [1.795]	16	17	1-103673-6	
		<div>1</div>	41.15 [1.620]	43.05 [1.695]	15	16	1-103673-5	
		<div>1</div>	38.61 [1.520]	40.51 [1.595]	14	15	1-103673-4	
		<div>1</div>	36.07 [1.420]	37.97 [1.495]	13	14	1-103673-3	
		<div>1</div>	33.53 [1.320]	35.43 [1.395]	12	13	1-103673-2	OBSOLETE
		<div>1</div>	30.99 [1.220]	32.89 [1.295]	11	12	1-103673-1	
		<div>1</div>	28.45 [1.120]	30.35 [1.195]	10	11	1-103673-0	
		<div>1</div>	25.91 [1.020]	27.81 [1.095]	9	10	103673-9	
		<div>1</div>	23.37 [.920]	25.27 [0.995]	8	9	103673-8	
		<div>1</div>	20.83 [.820]	22.73 [.895]	7	8	103673-7	
<div>1</div>	18.29 [.720]	20.19 [.795]	6	7	103673-6			
<div>1</div>	15.75 [.620]	17.65 [.695]	5	6	103673-5			
<div>1</div>	13.21 [.520]	15.11 [.595]	4	5	103673-4			
<div>1</div>	10.67 [.420]	12.57 [.495]	3	4	103673-3			
<div>1</div>	8.13 [.320]	10.03 [.395]	2	3	103673-2			
<div>1</div>	5.59 [.220]	7.49 [.295]	1	2	103673-1			
REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.		

4805 (1/15)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± - 1. PLC ± - 2. PLC ± 0.13[.005] 3. PLC ± - 4. PLC ± - ANGLES FINISH SEE TABLE
----------------------------	---

MATERIAL: HOUSING: FLAME RETARDENT LCP COLOR: BLACK CONTACTS: BRASS	SEE TABLE
--	-----------

DWN S. SHUEY	OSMAR91
CHK J. GESFORD	OSMAR91
APVD J. GESFORD	OSMAR91
NAME	HDR ASSY, RTANG, SINGLE ROW 2.54[.100] C/L 0.641[.025] SQ. POST, WITH PLZN & HOLD DOWNS, AMPMODU MTE
PRODUCT SPEC	108-25034
APPLICATION SPEC	114-25026
SIZE	A1
CAGE CODE	00779
DRAWING NO	103673
WEIGHT	-
CUSTOMER DRAWING	SCALE 4:1
SHEET 2	OF 2
REV W1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103673-2](#)