





P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER ECN-23-241256	07MAY2024	DB	BW


0.25 [.010]
MAX CUT-OFF



SECTION B-B



SECTION A-A
SCALE 8:1



RECOMMENDED
P.C.B. HOLES

- 1 SUPPLIED IN LOOSE PIECE FORM.
- 2 0.00254 [.000100] MIN THK TIN OVER 0.00254 [.000100] MIN THK COPPER, OR OVER 0.00127 [.000050] MIN NICKEL.
- 3 MATING TAB THK IS 0.81±0.025 [.032±.001].

1217080-1
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH
MATERIAL BRASS	- 2

DWN JR RUTH 3/30/98	CHK MS FEHER 3/30/98	APVD D BRATINA 3/30/98
PRODUCT SPEC	APPLICATION SPEC	114-2156
WEIGHT 0.000000	CUSTOMER DRAWING	SCALE 4:1

				RECEPTACLE, FASTON, 6.35/5.21 [.250/.205] SERIES, PC BOARD MOUNTED	
NAME	SIZE A3	CAGE CODE 00779	DRAWING NO C-1217080	RESTRICTED TO	REV D
SHEET 1 OF 1					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1217080-1](#)