


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	BI	ECO-20-004274	26MAR2021	RK	DR
	C	REVISED PER ECR-23-165796	28FEB2023	LP	DSC



AMP
WIRE RANGE
1/0 AWG
SOLID OR STRANDED

1. STAMP: AMP 1/0 W* APPROX AS SHOWN.
2. MATERIAL: COPPER PER ASTM B152.
3. FINISH: NICKEL PLATE 0.00762[.000300] MIN EXT THK PER SAE AMS-QQ-N-290
4. MATERIAL THK: 1.778±0.051[.070±.002]

50	LOOSE PIECE	132066-2
QTY	PACKAGE TYPE	PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX. RECOMMENDED OPERATING TEMPERATURE: 343°C [649°F]
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: NOT APPLICABLE
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE: 42.4-60.6mm ² [83,700-119,500] CIR MILS SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±0.127 (.005) 4 PLC ± ANGLES ±
MATERIAL	FINISH
2	3

DWN RAGHAVENDRA.K 06APR2020	CHK DANIEL.R 06APR2020	APVD DANIEL.R 06APR2020
PRODUCT SPEC 108-32046	APPLICATION SPEC 114-2162	WEIGHT -
CUSTOMER DRAWING		

NAME TERMINAL, RING TONGUE, STRATO-THERM HEAT RESISTANT, WIRE SIZE: 1/0 AWG			
SIZE A3	CAGE CODE 00779	DRAWING NO C-132066	RESTRICTED TO -
SCALE 2:1		SHEET 1 OF 1	REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[132066-2](#)