


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B3	REV PER ECR-22-149214	18AUG2022	LP	DSC

AMP  
WIRE RANGE





2/0 AWG  
SOLID OR STRANDED



- 1 STAMP "AMP 2/OW\* ", LOCATED APPROX AS SHOWN
- 2 NOTE DELETED
- 3 NOTE DELETED
- 4 MATERIAL:  
COPPER PER ASTM B152, ANNEALED
- 5 FINISH:  
NICKEL PLATE 0.00762[.000300] MIN EXT THK PER SAE AMS-QQ-N-290
- 6 MATERIAL THK: 2.007±0.076[.079±.003]

25	LOOSE PIECE	132104-2
QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 343°C [650°F]
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 60.6-76.3mm²[119,500-150,000] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 25JAN10		<div>TE Connectivity</div>				
DIMENSIONS: mm [INCHES]		CHK T MICHELUTTI 25JAN10						
<div></div>		APVD T MICHELUTTI 25JAN10		NAME  TERMINAL, RING TONGUE, STRATO-THERM, HR, SOLISTRAND, WIRE SIZE: 2/0 AWG				
		PRODUCT SPEC  —						
		APPLICATION SPEC  114-2162						
		WEIGHT  —						
MATERIAL <div></div>		FINISH <div></div>		SIZE A3	CAGE CODE 00779	DRAWING NO C-132104	RESTRICTED TO  —	
CUSTOMER DRAWING						SCALE 2:1	SHEET 1 of 1	REV B3

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[132104-2](#)