




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F4	REMOVE CAP BULGE	200CT2023	MC	HL




DETAIL E
(SCALE 2:1)




SECT. F-F
(SCALE 2:1)
ROTATED 90° CW

NO	3	18	75	440	9-1827231-6
NO	3	18	75	440	3-1827231-6
SEALANT	ROW	QTY	A	POS.	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
MM	
	0 PLC ± 0.25
	1 PLC ± 0.15
	2 PLC ± 0.10
	3 PLC ± 0.05
	4 PLC ± 0.0250
	ANGLES ± 3°
MATERIAL	FINISH

DWN S.CHIEIN	18MAY05	 TE Connectivity Ltd.			
CHK T.FUTATSUGI	18MAY05				
APVD W.KODAMA	18MAY05	NAME			
PRODUCT SPEC 108-5560		HARD TRAY ASSY FH 0.5BTB CONNECTOR 440POS REC 4H W/G-PLATE ON 2 ROW CAP			
APPLICATION SPEC		RESTRICTED TO			
WEIGHT		SIZE A3	CAGE CODE 00779	DRAWING NO C-1827231	REV F4
CUSTOMER DRAWING		SCALE 1:2		SHEET 1 OF 4	

4


3

2

1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—



BLACK	62.8	440	9-1827231-6
BLACK	62.8	440	3-1827231-6
CAP COLOR	B	POS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CHK APVD PRODUCT SPEC APPLICATION SPEC WEIGHT		NAME	
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		HARD TRAY ASSY FH 0.5BTB CONNECTOR 440POS REC 4H W/G-PLATE ON 2 ROW CAP	
0 PLC ± 0.25 1 PLC ± 0.15 2 PLC ± 0.10 3 PLC ± 0.05 4 PLC ± 0.0250 ANGLES ± 3°		FINISH		SIZE A3	
MATERIAL		1		CAGE CODE 00779	
2		CUSTOMER DRAWING		DRAWING NO C-1827231	
				RESTRICTED TO	
				SCALE 4:1	
				SHEET 2 OF 4	
				REV F4	

4


3

2

1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



NOTES

- 1 MATERIAL ; HOUSING : HIGH TEMP THERMO PLASTIC UL94V-0
CONTACT : COPPER ALLOY; SOLDER PEG : COPPER ALLOY
- 2 FINISH ; MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF
PRODUCT SPECIFICATION 108-5560;
SOLDER TAIL OF SIGNAL & GROUND CONTACTS : GOLD FLASH;
SOLDER PEG : TIN OVER Ni
- 3 THIS POSITION IS GROUND CIRCUIT.


THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± 0.25 1 PLC ± 0.15 2 PLC ± 0.10 3 PLC ± 0.05 4 PLC ± 0.0250 ANGLES $\pm 3'$
MATERIAL	FINISH
1	2

CHK	DWN	TE Connectivity Ltd.
APVD	NAME	
PRODUCT SPEC	SIZE	
APPLICATION SPEC	CAGE CODE	
WEIGHT	DRAWING NO	RESTRICTED TO
CUSTOMER DRAWING	A3 00779 C-1827231	
SCALE 4:1	SHEET 3 OF 4	REV F4





REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



REFERENCE P.C.BOARD LAYOUT

59.5	440	9-1827231-6
59.5	440	3-1827231-6
H	POS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		 TE Connectivity Ltd.	
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.25 1 PLC ± 0.15 2 PLC ± 0.10 3 PLC ± 0.05 4 PLC ± 0.0250 ANGLES ± 3°	
		NAME HARD TRAY ASSY FH 0.5BTB CONNECTOR 440POS REC 4H W/G-PLATE ON 2 ROW CAP	
MATERIAL		SIZE	RESTRICTED
FINISH 		CAGE CODE A3 00779	DRAWING NO C-1827231
WEIGHT 		CUSTOMER DRAWING SCALE 4:1 SHEET 4 OF 4 REV F4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[9-1827231-6](#)