






REVISIONS 変更					
P	LTR	DESCRIPTION		DATE	APVD
	F	REVISED PER ECR-22-142637		16JUN2022	RI TS




TRADE MARK  
TOOLING ID MARK  
ON OUTER SURFACE



MATE WITH 0.5t TAB

D S 4	AWG#30~#28 0.05~0.09mm <sup>2</sup>	Φ 0.6~Φ 1.2	COPPER ALLOY,FINISH:CONTACT AREA Au 0.2μ m MIN,OVER Ni 1.27μ m MIN	1827569-4
D S	AWG#30~#28 0.05~0.09mm <sup>2</sup>	Φ 0.6~Φ 1.2	COPPER ALLOY,FINISH:CONTACT AREA Au 0.38μ m MIN,OVER Ni 1.27μ m MIN	1827569-2
SERIES MARK	WIRE RANGE	INSULATION DIA	MATERIAL	PART No.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.KUDO	04MAR2005	 TE Connectivity	
		CHK D.MITSUGI	04MAR2005		
		APVD D.MITSUGI	04MAR2005	NAME 名称  DYNMIC D1000 SERIES REC CONTACT (S TYPE) REEL	
		PRODUCT SPEC 製品規格 108-78268			
		APPLICATION SPEC 取付適用規格 114-5377		SIZE CAGE CODE DRAWING NO 番号 A300779C-1827569	
		WEIGHT 0			
CUSTOMER DRAWING		SCALE 尺度 10:1		SHEET 1 OF 1	REV F

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1827569-4](#)