






printed on 3 Feb 2021 16:39 (China Standard Time) from TE304429


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		CI	REVISED	14JUL2010	HMR	TM
			D	REVISED	17DEC2012	H.M	N.Y
			DI	REVISED	03FEB2021	F.Z	R.B

D

D



40POS(X-KEY):1-1871315-0



RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1

C

1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC
POLYESTER(94V-0)

COLOR: BLACK

CONTACT: PRE-TIN COPPER ALLOY

RETENTION LEG: PRE-TIN COPPER ALLOY

2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER
SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.

40	X	19	38.0	41.0	42.6	PRE-TIN	1-1871315-0
34	Y	16	32.0	35.0	36.6	PRE-TIN	2-1871315-7
34	X	16	32.0	35.0	36.6	PRE-TIN	1-1871315-7
32	X	15	30.0	33.0	34.6	PRE-TIN	1-1871315-6
30	X	14	28.0	31.0	32.6	PRE-TIN	1-1871315-5
28	X	13	26.0	29.0	30.6	PRE-TIN	1-1871315-4
26	X	12	24.0	27.0	28.6	PRE-TIN	1-1871315-3
24	X	11	22.0	25.0	26.6	PRE-TIN	1-1871315-2
22	X	10	20.0	23.0	24.6	PRE-TIN	1-1871315-1
POS	KEY	n	A	B	C	FINISH	PART NO

B

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	T. KUDO	23AUG2005			
		CHK	D. MITSUGI	23AUG2005			
		APVD	D. MITSUGI	23AUG2005	NAME		
		PRODUCT SPEC	-	108-78298 108-137366	DYNAMIC D1100 SERIES HDR ASSY, V-TYPE, PRE-TIN 22~40POS		
		APPLICATION SPEC	114-5377		SIZE		
		WEIGHT	-		A300779C=1871315		
		CUSTOMER DRAWING			SCALE		
					2:1		
					SHEET		
					1 OF 3		
					REV		
					DI		

A

printed on 3 Feb 2021 16:39 (China Standard Time) from TE304429

D

B

A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20













© COPYRIGHT 2020 TE Connectivity. All Rights Reserved. ALL RIGHTS RESERVED.

LOC
J

DIST
-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



22POS(X-KEY)
1-1871315-1


24POS(X-KEY)
1-1871315-2

26POS(X-KEY)
1-1871315-3

28POS(X-KEY)
1-1871315-4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
TBD

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.5
2 PLC ±0.13
3 PLC ±0.013
4 PLC ±0.0001
ANGLES ±-

FINISH
-

DWN T. KUDO 03DEC2020

CHK D. MITSUGI 23AUG2005

APVD D. MITSUGI 23AUG2005

PRODUCT SPEC 108-78298
108-137366

APPLICATION SPEC

114-5377

WEIGHT -

CUSTOMER DRAWING






TE Connectivity

NAME
DYNAMIC D1100 SERIES
HDR ASSY, V-TYPE, PRE-TIN
22~40POS

SIZE CAGE CODE DRAWING NO RESTRICTED TO
A300779C=1871315 -

SCALE 2:1 SHEET 2 OF 3 REV D1

$$-2X_n \equiv A -$$


34POS(X-KEY)
1-1871315-7

NOTES: 2-1871315-7 IS SYMMETRY WITH 1-1871315-7 FOR KEY WAY

CUSTOMER DRAWING

CUSTOMER DRAWING

3	REV D I
---	---------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1871315-3](#) [2-1871315-7](#) [1-1871315-4](#)