



020/060 56P HEADER ASSY TYPE A

D

C

B


A



P/NO	2188220-1 2-2188220-1	1-2188220-1 3-2188220-1	4-2188220-2	5-2188220-3
CODE	A	B	C	D
SHAPE				

NOTE
1. GENERAL TOLERANCE: ± 0.3 , $\pm 2.0^\circ$
2. THE MATING PLUG ASS'Y P/N:
X-2188225-X

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED (ECR-23-164942)	27JUN2023	DG	KT
	B1	REVISED (ECR-23-192831)	17NOV2023	DG	KT
	B2	REVISED (ECR-24-199726)	08FEB2024	DG	YH



PCB LAY-OUT
*P.C.B THICKNESS : $1.6 \pm 0.05\text{mm}$
*APPLICABLE P.C.B MOUNT TYPE : BOLTING TYPE
*SCREW ASSEMBLE TORQUE : MAX 2.0kgf.cm




ASS'Y P/N	DESCRIPTION	PACKING
9-2188220-2	56P HEADER ASS'Y(D)_TYPE B	PAPER BOX
7-2188220-2	56P HEADER ASS'Y(C)_TYPE B	CLEAR TRAY /PAPER BOX
6-2188220-2	56P HEADER ASS'Y(C)_TYPE B	BLACK TRAY /PAPER BOX
1-2188220-2	56P HEADER ASS'Y(B)_TYPE B	BLACK TRAY /PAPER BOX
2188220-2	56P HEADER ASS'Y(A)_TYPE B	PAPER BOX
5-2188220-3	56P HEADER ASS'Y(D)_TYPE A	PAPER BOX
4-2188220-2	56P HEADER ASS'Y(C)_TYPE A	PAPER BOX
3-2188220-1	56P HEADER ASS'Y(B)_TYPE A	PAPER BOX
2-2188220-1	56P HEADER ASS'Y(A)_TYPE A	PAPER BOX
1-2188220-1	56P HEADER ASS'Y(B)_TYPE A	PLASTIC BOX
2188220-1	56P HEADER ASS'Y(A)_TYPE A	PLASTIC BOX

NO	COLOR	MATERIAL	DESCRIPTION	Q'TY
6	BLACK	PA46-GF15	020/060 56P ALIGNMENT PLATE-WAVELESS	1
5	NATURAL	PA66-GF15	020/060 56P ALIGNMENT PLATE	1
4	POST-TIN	C2680 H04	060 TAB CONTACT(L)	16
3	POST-TIN	C2680 H04	060 TAB CONTACT(S)	16
2	POST-TIN	C2680 H04	020 TAB CONTACT(L)	14
1	BLACK	LCP-GF30	HEADER HSG(D)-WAVELESS	1
	GRAY	LCP-GF30	HEADER HSG(B)-WAVELESS	1
	BLACK	LCP-GF30	HEADER HSG(A)-WAVELESS	1
	NATURAL	LCP-GF30	HEADER HSG(C)-WAVELESS	1
	NATURAL	LCP-GF30	HEADER HSG(C)	1
	NATURAL	LCP-GF30	HEADER HSG(B)	1
	NATURAL	LCP-GF30	HEADER HSG(A)	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YJ KIM 17NOV2015	TE Connectivity	
DIMENSIONS: mm		CHK KT LIM 17NOV2015	NAME 020/060 56P HEADER ASSY HORIZONTAL TYPE	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD HG CHO 17NOV2015	SIZE A2	
0 PLC ±0.5		PRODUCT SPEC	CAGE CODE	
1 PLC ±0.13		APPLICATION SPEC	DRAWING NO	
2 PLC ±0.013		WEIGHT	RESTRICTED TO	
3 PLC ±0.001		CUSTOMER DRAWING	SCALE 2:1	
4 PLC ±0.001		SHEET 1 OF 2	REV B2	
ANGLES ±				
FINISH				

020/060 56P HEADER ASSY TYPE B

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



P/NO	2188220-2	1-2188220-2	6-2188220-2 7-2188220-2	9-2188220-2
CODE	A	B	C	D
SHAPE				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YJ KIM	17NOV2015		
DIMENSIONS:		CHK KT LIM	17NOV2015		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD HG CHO	17NOV2015	NAME 020/060 56P HEADER ASSY HORIZONTAL TYPE	
	0 PLC ± 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001	PRODUCT SPEC	-	SIZE	CAGE CODE
	ANGLES ± FINISH	APPLICATION SPEC	-	A2	-
MATERIAL	-	WEIGHT	-	DRAWING NO	RESTRICTED TO
-	-	CUSTOMER DRAWING	-	C-2188220	-
		SCALE	2:1	SHEET	2 OF 2
		REV	B2		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2188220-2](#)