






060/110/250

HYB 38P COVER ASSY TYPE A

PN.2219215-X

SCALE 1:1
<ISO VIEW>








SECTION A-A

060/110/250

HYB 38P COVER ASSY TYPE B

PN.2-2219215-X

SCALE 1:1
<ISO VIEW>



SECTION B-B

NOTES

1. GENERAL TOLERANCE : ± 0.3 , $\pm 3^\circ$
2. DELIVERY CONDITION : CPA IN PRE-LOCKED POSITION
3. APPLICABLE PLUG : X-2219210-X HYB SEALED 38POS PLUG ASSY
4. SEE SHEET 2 OF 2 FOR THE WITHOUT CPA TYPE

REVISONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED (ECR-15-008693)	09.JUN.'15	EW	HG
B1		REVISED (ECR-16-003970)	19.MAY.'16	EW	KT
B2		REVISED (ECR-17-008059)	03.JUL.'17	EW	KT
C		REVISED (ECR-20-001387)	01FEB2020	EW	Y.J

		ASSY DISCRIPTION		ASSY P/N	
7	BLACK	PBT	CPA FOR HYB 38POS COVER ASSY	0-2219215-1	HYBRID SEALED 38POS COVER ASSY TYPE A
6	RED	PBT	CPA FOR HYB 38POS COVER ASSY	-	HYBRID SEALED 38POS COVER ASSY TYPE A
5	GRAY	PBT	CPA FOR HYB 38POS COVER ASSY	I	HYBRID SEALED 38POS COVER ASSY TYPE A
4	GRAY	PBT-GF20	HYB 38P COVER HSG TYPE B	-	HYBRID SEALED 38POS COVER ASSY TYPE B
3	BLACK	PBT-GF20	HYB 38P COVER HSG TYPE B	-	HYBRID SEALED 38POS COVER ASSY TYPE B
2	GRAY	PBT-GF20	HYB 38P COVER HSG TYPE A	-	HYBRID SEALED 38POS COVER ASSY TYPE B
1	BLACK	PBT-GF20	HYB 38P COVER HSG TYPE A	I	HYBRID SEALED 38POS COVER ASSY TYPE B
NO		COLOR/FINISH	MATERIAL	DESCRIPTION	QT'YQT'YQT'YQT'YQT'YQT'Y

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CHP YD LEE	TE Connectivity	
DIMENSIONS:		KT ILM		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME	
	0 PLC $\pm$	108-61230	HYB SEALED 38POS COVER ASSEMBLY	
	1 PLC $\pm$	APPLICATION SPEC		
	2 PLC $\pm$		SIZE	
	3 PLC $\pm$		CAGE CODE	
	4 PLC $\pm$		DRAWING NO	
	ANGLES		RESTRICTED TO	
	FINISH		A1	
MATERIAL		WEIGHT	C=2219215	
SEE TABLE		CUSTOMER DRAWING	SCALE	






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

060/110/250

HYB 38P COVER W/O CPA "H" TYPE

PN.1-2219215-X

SCALE 1:1
<ISO VIEW>








SECTION C-C

B2060/110/250

HYB 38P COVER W/O CPA "L" TYPE

PN.3-2219215-2

SCALE 1:1
<ISO VIEW>



SECTION K-K

B2	3	BLACK	PBT-GF20	38P COVER HSG W/O CPA "L" TYPE	3-2219215-2
	2	GRAY	PBT-GF20	38P COVER HSG W/O CPA "H" TYPE	1-2219215-3
	1	BLACK	PBT-GF20	38P COVER HSG W/O CPA "H" TYPE	1-2219215-2
	NO	COLOR/FINISH	MATERIAL	DESCRIPTION	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN		 TE Connectivity	
			CHK			
DIMENSIONS:			TOLERANCES UNLESS OTHERWISE SPECIFIED		NAME	
mm			APVD		HYB SEALED 38POS COVER ASSEMBLY	
			PRODUCT SPEC			
			108-61230			
			APPLICATION SPEC			
					SIZE	
					CAGE CODE	
					DRAWING NO	
					RESTRICTED TO	
MATERIAL			WEIGHT		A1 - C=2219215	
SEE TABLE			CUSTOMER DRAWING		SCALE 1:1 SHEET 2 OF 2 REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2219215-1](#)