




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER ECR-21-100686	10MAR2021	SK	DZ

KEYING A SHOWN FOR 6 POS






SECTION A-A
FOR 2~5P




SECTION A-A
FOR 6~10P

- 1 MATERIAL:
HOUSING :THERMOPLASTIC, UL94 V0;
REC. CONTACT : PHOS-BRONZE,PRE-TIN .
- 2.PRODUCT COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS
OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING
CONNECTION DETAILED IN IEC 60335-1, SECTION 30 (GWT).
3. MATING PARTS PLEASE SEE TABLE IN PAGE1 AND PAGE2.
- 4 OBSOLETE.





KEY A



KEY B

KEYING ID



2-2232829-0	2-2232826-0	9.0	21.3	20.6	10	A	NATURAL	2-2232979-0
1-2232829-9	1-2232826-9	8.0	19.3	18.6	9			1-2232979-9
1-2232829-8	1-2232826-8	7.0	17.3	16.6	8			1-2232979-8
1-2232829-7	1-2232826-7	6.0	15.3	14.6	7			1-2232979-7
1-2232829-6	1-2232826-6	5.0	13.3	12.6	6			1-2232979-6
1-2232829-5	1-2232826-5	4.0	11.3	10.6	5			1-2232979-5
1-2232829-4	1-2232826-4	3.0	9.3	8.6	4			1-2232979-4
1-2232829-3	1-2232826-3	2.0	7.3	6.6	3			1-2232979-3
1-2232829-2	1-2232826-2	1.0	5.3	4.6	2			1-2232979-2
MATING PART_SMT	MATING PART_TH	DIM.C	DIM.B	DIM.A	POS.	KEYING	COLOR	ASSEMBLY PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±0.15

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH

1

DWN CANDY XU 1SEP2017

CHK DANIEL. Z 4SEP2017

APVD DANIEL. Z 4SEP2017

PRODUCT SPEC 108-106266

APPLICATION SPEC 114-106266

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

PLUG ASSEMBLY, SGI 2.0mm

SIZE A3

CAGE CODE 00779

DRAWING NO C-2232979

RESTRICTED TO -

SCALE 8:1


SHEET 1 OF 3

REV B1

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20
© COPYRIGHT 20		BY -		ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

3-2232829-0	3-2232826-0	9.0	21.3	20.6	10	B	NATURAL	3-2232979-0	
2-2232829-9	2-2232826-9	8.0	19.3	18.6	9			2-2232979-9	
2-2232829-8	2-2232826-8	7.0	17.3	16.6	8			2-2232979-8	
2-2232829-7	2-2232826-7	6.0	15.3	14.6	7			2-2232979-7	
2-2232829-6	2-2232826-6	5.0	13.3	12.6	6			2-2232979-6	
2-2232829-5	2-2232826-5	4.0	11.3	10.6	5			2-2232979-5	
2-2232829-4	2-2232826-4	3.0	9.3	8.6	4			2-2232979-4	
2-2232829-3	2-2232826-3	2.0	7.3	6.6	3			2-2232979-3	
2-2232829-2	2-2232826-2	1.0	5.3	4.6	2			2-2232979-2	
MATING PART_SMT	MATING PART_TH	DIM.C	DIM.B	DIM.A	POS.	KEYING	COLOR	ASSEMBLY PART NO.	
4-2232829-0	4-2232826-0	9.0	21.3	20.6	10	A	BLACK	4-2232979-0	
3-2232829-9	3-2232826-9	8.0	19.3	18.6	9			3-2232979-9	
3-2232829-8	3-2232826-8	7.0	17.3	16.6	8			3-2232979-8	
3-2232829-7	3-2232826-7	6.0	15.3	14.6	7			3-2232979-7	
3-2232829-6	3-2232826-6	5.0	13.3	12.6	6			3-2232979-6	
3-2232829-5	3-2232826-5	4.0	11.3	10.6	5			3-2232979-5	
3-2232829-4	3-2232826-4	3.0	9.3	8.6	4			3-2232979-4	
3-2232829-3	3-2232826-3	2.0	7.3	6.6	3			3-2232979-3	
3-2232829-2	3-2232826-2	1.0	5.3	4.6	2			3-2232979-2	
MATING PART_SMT	MATING PART_TH	DIM.C	DIM.B	DIM.A	POS.	KEYING	COLOR	ASSEMBLY PART NO.	
5-2232829-0	5-2232826-0	9.0	21.3	20.6	10	B	BLACK	5-2232979-0	
4-2232829-9	4-2232826-9	8.0	19.3	18.6	9			4-2232979-9	
4-2232829-8	4-2232826-8	7.0	17.3	16.6	8			4-2232979-8	
4-2232829-7	4-2232826-7	6.0	15.3	14.6	7			4-2232979-7	
4-2232829-6	4-2232826-6	5.0	13.3	12.6	6			4-2232979-6	
4-2232829-5	4-2232826-5	4.0	11.3	10.6	5			4-2232979-5	
4-2232829-4	4-2232826-4	3.0	9.3	8.6	4			4-2232979-4	
4-2232829-3	4-2232826-3	2.0	7.3	6.6	3			4-2232979-3	
4-2232829-2	4-2232826-2	1.0	5.3	4.6	2			4-2232979-2	
MATING PART_SMT	MATING PART_TH	DIM.C	DIM.B	DIM.A	POS.	KEYING	COLOR	ASSEMBLY PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CANDY XU 1SEP2017		 TE Connectivity		
		CHK DANIEL. Z 4SEP2017				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PLUG ASSEMBLY, SGI 2.0mm		
		0 PLC ±- 1 PLC ±- 2 PLC ±0.15 3 PLC ±- 4 PLC ±- ANGLES ±-				
MATERIAL 		FINISH 		PRODUCT SPEC 108-106266		RESTRICTED TO -
				APPLICATION SPEC 114-106266		
				WEIGHT -		
CUSTOMER DRAWING				SIZE A3	CAGE CODE 00779	DRAWING NO C-2232979
				SCALE 8:1	SHEET 2 OF 3	REV B1

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20



COPYRIGHT 20


BY -

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1 SEE SHEET1			


KEYING A SHOWN FOR 2 THRU 10 POS.




2POS.




3POS.




4POS.




5POS.




6POS.




7POS.







8POS.



9POS.



10POS.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CANDY XU	1SEP2017	 TE Connectivity	
		CHK DANIEL. Z	4SEP2017		
		APVD DANIEL. Z	4SEP2017	NAME PLUG ASSEMBLY, SGI 2.0mm	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		-	
		0 PLC	±-	SIZE	
		1 PLC	±-	CAGE CODE	
		2 PLC	±0.15	DRAWING NO	
		3 PLC	±-	RESTRICTED TO	
		4 PLC	±-		
MATERIAL		FINISH		A300779C-2232979	
				SCALE 8:1 SHEET 3 OF 3 REV B1	
		CUSTOMER DRAWING			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2232979-8](#)