






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	30MAY2022	F.Z	R.B
	B	REVISED PER ECR-22-162100	23DEC2022	C.C	R.B
	C	REVISED PER ECR-23-170031	22MAR2023	C.C	R.B
	D	Obsolete 2-2390471-1	29APR2024	R.W	R.B




16	Y	15	30.0	33.0	34.6	2-2390471-3
16	X	15	30.0	33.0	34.6	1-2390471-3
14	Y	13	26.0	29.0	30.6	2-2390471-2
14	X	13	26.0	29.0	30.6	1-2390471-2
12	Y	11	22.0	25.0	26.6	2-2390471-1
12	X	11	22.0	25.0	26.6	1-2390471-1
10	Y	9	18.0	21.0	22.6	2-2390471-0
10	X	9	18.0	21.0	22.6	1-2390471-0
8	Y	7	14.0	17.0	18.6	2-2390471-8
8	X	7	14.0	17.0	18.6	1-2390471-8
4	Y	3	6.0	9.0	10.6	2-2390471-4
4	X	3	6.0	9.0	10.6	1-2390471-4
POS	KEY	n	A	B	C	PART NO

NOTES










1	MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC POLYESTER(UL94V-0),COLOR: BLACK CONTACT: COPPER ALLOY RETENTION LEG: PRE-TIN COPPER ALLOY	Obsolete
2	FINISH (ALL OVER): TIN PLATING: 1.0umMIN AFTER NICKEL PLATING WITH 1.27umMIN	
3.	THE KEYING ARRANGEMENTOF "Y" IS SYMMETIC WITH "X"	
4.	THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOWN THE OUTLINE, AND DON'T SHOWN DETAIL	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 30MAY2022 FISHER ZHU CHK 30MAY2022 RICK BIAN APVD 30MAY2022 RICK BIAN PRODUCT SPEC 108-78298 APPLICATION SPEC 114-5377 WEIGHT		 TE Connectivity							
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±3°		NAME DYNAMIC D1100S SERIES HDR ASSY, V-TYPE, 4-16POS, TIN -							
MATERIAL 		FINISH 		SIZE A3		CAGE CODE 00779		DRAWING NO C-2390471		RESTRICTED TO -	
CUSTOMER DRAWING						SCALE 4:1		SHEET 1 OF 3		REV D	

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



4POS X-KEY
PN: 1-2390471-4

8POS X-KEY
PN: 1-2390471-8

16POS X-KEY
PN: 1-2390471-3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER ZHU 30MAY2022	 TE Connectivity		
DIMENSIONS: mm		CHK RICK BIAN 30MAY2022			
		APVD RICK BIAN 30MAY2022	NAME DYNAMIC D1100S SERIES HDR ASSY, V-TYPE, 4-16POS, TIN -		
		PRODUCT SPEC SEE SEET1/3			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC SEE SEET1/3	SIZE A3		
MATERIAL SEE SEET1/3		WEIGHT CUSTOMER DRAWING			
FINISH SEE SEET1/3		SCALE 4:1	CAGE CODE 00779		DRAWING NO C-2390471
		SHEET 2 OF 3	RESTRICTED TO -		REV D

4







3

2

1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



12POS X-KEY
PN:1-2390471-1

14POS X-KEY
PN:1-2390471-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER ZHU 30MAY2022	 TE Connectivity		
		CHK RICK BIAN 30MAY2022			
DIMENSIONS: mm		APVD RICK BIAN 30MAY2022	NAME DYNAMIC D1100S SERIES HDR ASSY, V-TYPE, 4-16POS, TIN -		
		PRODUCT SPEC SEE SEET1/3			
		APPLICATION SPEC SEE SEET1/3			
MATERIAL SEE SEET1/3		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-2390471
		FINISH SEE SEET1/3	RESTRICTED TO -		
			SCALE 4:1	SHEET 3 OF 3	REV D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2390471-8](#)