





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	30MAY2022	F.Z	R.B
	B	REVISED PER ECR-22-162100	23DEC2022	C.C	R.B
	C	REVISED PER ECR-23-170031	22MAR2023	C.C	R.B
	D	Obsolete 2-2390471-1	29APR2024	R.W	R.B



	16	Y	15	30.0	33.0	34.6	2-2390471-3
	16	X	15	30.0	33.0	34.6	1-2390471-3
	14	Y	13	26.0	29.0	30.6	2-2390471-2
	14	X	13	26.0	29.0	30.6	1-2390471-2
e	12	Y	11	22.0	25.0	26.6	2-2390471-1
	12	X	11	22.0	25.0	26.6	1-2390471-1
	10	Y	9	18.0	21.0	22.6	2-2390471-0
	10	X	9	18.0	21.0	22.6	1-2390471-0
	8	Y	7	14.0	17.0	18.6	2-2390471-8
	8	X	7	14.0	17.0	18.6	1-2390471-8
	4	Y	3	6.0	9.0	10.6	2-2390471-4
	4	X	3	6.0	9.0	10.6	1-2390471-4
	POS	KEY	n	A	B	C	PART NO


NOTES


1 MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC POLYESTER(UL94V-0),COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: PRE-TIN COPPER ALLOY

2 FINISH (ALL OVER): TIN PLATING: 1.0umMIN
AFTER NICKEL PLATING WITH 1.27umMIN

3. THE KEYING ARRANGEMENT OF "Y" IS SYMMETIC WITH "X"










4. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOWN
THE OUTLINE, AND DON'T SHOWN DETAIL



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 30MAY2022 FISHER ZHU CHK 30MAY2022 RICK BIAN APVD 30MAY2022 RICK BIAN PRODUCT SPEC 108-78298 APPLICATION SPEC 114-5377 WEIGHT CUSTOMER DRAWING		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±3°		NAME DYNAMIC D1100S SERIES HDR ASSY, V-TYPE, 4-16POS, TIN -	
		MATERIAL 		RESTRICTED TO -	
FINISH 		SIZE A3		CAGE CODE 00779	DRAWING NO C-2390471
		SCALE 4:1		SHEET 1 OF 3	REV D

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			









4POS X-KEY
PN: 1-2390471-4

8POS X-KEY
PN: 1-2390471-8

16POS X-KEY
PN: 1-2390471-3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER ZHU 30MAY2022	 TE Connectivity		
		CHK RICK BIAN 30MAY2022			
		APVD RICK BIAN 30MAY2022	NAME DYNAMIC D1100S SERIES HDR ASSY, V-TYPE, 4-16POS, TIN		
		PRODUCT SPEC SEE SEET1/3			
		APPLICATION SPEC SEE SEET1/3	SIZE A3		
		WEIGHT			
MATERIAL SEE SEET1/3		FINISH SEE SEET1/3	CAGE CODE 00779		DRAWING NO C-2390471
		CUSTOMER DRAWING		SCALE 4:1	SHEET 2 OF 3
				REV D	RESTRICTED TO -

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



12POS X-KEY
PN:1-2390471-1

14POS X-KEY
PN:1-2390471-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER ZHU 30MAY2022	 TE Connectivity						
		CHK RICK BIAN 30MAY2022							
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD RICK BIAN 30MAY2022	NAME DYNAMIC D1100S SERIES HDR ASSY, V-TYPE, 4-16POS, TIN -						
	0 PLC ± 0.2 1 PLC ± 0.2 2 PLC ± 0.2 3 PLC ± 0.2 4 PLC ± 0.2 ANGLES ± 3°	PRODUCT SPEC SEE SEET1/3							
MATERIAL SEE SEET1/3	FINISH SEE SEET1/3	APPLICATION SPEC SEE SEET1/3	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO		
		WEIGHT	A3	00779	C-2390471		-		
CUSTOMER DRAWING			SCALE	4:1		SHEET	3 OF 3	REV	D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2390471-4](#) [1-2390471-4](#)