






P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	31MAY2022	F.Z	R.B
	B		16APR2024	R.W	R.B



1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC POLYSTER(UL94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: PRE-TIN COPPER ALLOY
2. FINISH (ALL OVER): NICKEL PLATING 1.27umMIN.
3. FINISH (CONTACT TAB): GOLD PLATING: 0.38umMIN.
(CONTACT TAIL): TIN PLATING: 1.0umMIN.
4. THE KEYING ARRANGEMENT OF "Y" IS SYMMETIC WITH "X"
5. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOWN THE OUTLINE, AND DON'T SHOWN DETAIL

16	Y	15	30.0	33.0	34.6	2-2394617-3
16	X	15	30.0	33.0	34.6	1-2394617-3
10	Y	9	18.0	21.0	22.6	2-2394617-0
10	X	9	18.0	21.0	22.6	1-2394617-0
8	Y	7	14.0	17.0	18.6	2-2394617-8
8	X	7	14.0	17.0	18.6	1-2394617-8
4	Y	3	6.0	9.0	10.6	2-2394617-4
4	X	3	6.0	9.0	10.6	1-2394617-4
POS	KEY	n	A	B	C	PART NO



10POS PN: 1-2394617-0

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.3 3 PLC ±0.3 4 PLC ±0.3 ANGLES ±3°
MATERIAL	FINISH

DWN	31MAY2022
CHK	31MAY2022
APVD	31MAY2022
PRODUCT SPEC	108-78268
APPLICATION SPEC	114-5377
WEIGHT	
CUSTOMER DRAWING	
















TE TE Connectivity


NAME: DYNAMIC D1100 SERIES
HDR ASSY, 4-10POS, V-TYPE, AU-PL

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2394617	-


SCALE: 2:1 SHEET: 1 OF 3 REV: B


P	LTR	DESCRIPTION	DATE	DWN	APVD



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER ZHU 31MAY2022		 TE Connectivity	
DIMENSIONS: mm		CHK RICK BIAN 31MAY2022			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD RICK BIAN 31MAY2022	
		0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.3 3 PLC ±0.3 4 PLC ±0.3 ANGLES ±3°		NAME DYNAMIC D1100 SERIES HDR ASSY, 4-10POS, V-TYPE, AU-PL -	
MATERIAL		FINISH		PRODUCT SPEC SEE SHEET1/2	
				APPLICATION SPEC SEE SHEET1/2	
				WEIGHT	
				CUSTOMER DRAWING	
				SCALE 4:1	
				SHEET 2 OF 3	
				REV B	

P	LTR	DESCRIPTION	DATE	DWN	APVD



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER ZHU 31MAY2022	 TE Connectivity			
DIMENSIONS: mm		CHK RICK BIAN 31MAY2022	NAME DYNAMIC D1100 SERIES HDR ASSY, 4-10POS, V-TYPE, AU-PL -			
		APVD RICK BIAN 31MAY2022				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC SEE SHEET1/2				
0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.3 3 PLC ±0.3 4 PLC ±0.3 ANGLES ±3°		APPLICATION SPEC SEE SHEET1/2				
MATERIAL	FINISH	WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-2394617	RESTRICTED TO -
		CUSTOMER DRAWING			SCALE 2:1	SHEET 3 OF 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2394617-8](#) [2-2394617-8](#)